

Bulk Cable Specification

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH (+10% / -0%)
RG59A-100	COIL	LOGO BAG	100 FT.
RG59A-500	SPOOL	STRETCH WRAP, CARD BOARD, OR OTHER	500 FT.
RG59A-1K	SPOOL	STRETCH WRAP, CARD BOARD, OR OTHER	1,000 FT.



75 OHM IMPEDANCE.

CENTER CONDUCTOR: 22 AWG. (7X30) BARE COMPACTED COPPER.

SHIELDING: BARE COPPER BRAID (95% COVERAGE).

INSULATION: FOAM POLYETHYLENE.

JACKET: BLACK PVC.

OPERATING TEMPERATURE: -40°C - +80°C.

NOMINAL ATTENUATION		
MHz	Db/100ft	Db/100m
50	2.1	6.9
100	3.0	9.8
200	4.5	14.8
400	6.6	21.7
1,000	11.9	39.0

NOTE:

SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC