

Bulk Cable Specification

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH (+ 10% / -0%)
RG59B-100	COIL	LOGO BAG	100 FT.
RG59B-500	SPOOL	STRETCH WRAP, CARD BOARD, OR OTHER	500 FT.
RG59B-1K	SPOOL	STRETCH WRAP, CARD BOARD, OR OTHER	1,000 FT.



75 OHM IMPEDANCE.

CENTER CONDUCTOR: 22 AWG. SOLID BARE COPPER COVERED STEEL.

SHIELDING: BARE COPPER BRAID (95% COVERAGE).

INSULATION: POLYETHYLENE.

JACKET: BLACK PVC.

OPERATING TEMPERATURE: -40°C - +80°C.

NOMINAL ATTENUATION		
MHz	Db/100ft	Db/100m
50	2.4	7.9
100	3.4	11.2
200	4.9	16.1
400	7.0	23.0
1,000	12.0	39.4

NOTE:
SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC