


**Bulk Cable Specification**

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
RG62A-100	COIL	BAG	100 FT.
RG62A-500	SPOOL	STRETCH WRAP	500 FT.
RG62A-1K	SPOOL	STRETCH WRAP	1,000 FT.



93 OHM IMPEDANCE.

CENTER CONDUCTOR: 22 AWG SOLD BARE  
COPPER COVERED STEEL

SHIELDING: BARE COPPER BRAID (95% COVERAGE).

INSULATION: SEMI-SOLID POLYETHYLENE.

JACKET: BLACK PVC.

OPERATING TEMPERATURE: -40°C - +80°C.

NOMINAL ATTENUATION		
MHz	Db/100ft	Db/100m
50	1.9	6.2
100	2.7	8.9
200	3.8	12.5
400	5.3	17.4
1,000	8.7	28.5

NOTE:

SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC