


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REPLACES SFODFC-01-OD1	6/24/14	D. CASTRO



PART NUMBER	LENGTH	
	METERS	[FEET]
SFODFC-01	1.0	[3.3]
SFODFC-02	2.0	[6.6]
SFODFC-03	3.0	[9.8]
SFODFC-04	4.0	[13.1]
SFODFC-05	5.0	[16.4]

NOTES:

- CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS DRAWN BY C.McCORMICK	DATE 01/02/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CHECKED BY DFP	DATE 01/19/01		CATEGORY FIBER OPTICS		
	APPROVED BY R.CARRICK	DATE 01/19/01	PRODUCT DESCRIPTION CA FC-FC 9/125 DUPLEX			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. SFODFC
SCALE: NONE		CAD FILE: SFODFC.SLDDRW		SHEET 1 OF 1		