


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/7/11	D.GRIFFIN



2X LC INDUSTRIAL DUPLEX CONNECTORS, IP66/67

2 COUNT 9/125 BREAKOUT CABLE
CORE LOCKED OUTER CABLE, INDOOR/OUTDOOR,
JACKET: BLACK

PART NUMBER	LENGTH	
	METERS	FEET
SFODLC-IND-01	1.0	[3.28]
SFODLC-IND-03	3.0	[9.84]
SFODLC-IND-05	5.0	[16.40]
SFODLC-IND-10	10.0	[32.80]

NOTES:

- CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- PACKAGING:
INDIVIDUALLY PACKAGE EACH ASSEMBLY
IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS DRAWN BY D. CASTRO CHECKED BY D. GUITTADAURO APPROVED BY D. GALLAGHER	DATE 3/31/11 4/1/11 4/1/11	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY FIBER OPTIC
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION CA LC-LC 9/125 IND DPX
	SIZE A	FSCM NO. 43321	DWG. NO. SFODLC-IND

SCALE: NONE | CAD FILE: SFODLC-IND.SLDDRW | SHEET 1 OF 1