


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/07	D.FRISIELLO
B	ECN 7306: ADD ORANGE, SHEET 2, REMOVE YELLOW, REVISE ROHS, FORMAT	2/25/14	D.FRISIELLO



NOTES:

CABLE CHARACTERISTICS:

9/125 SINGLE MODE DUPLEX FIBER ZIPCORD
 JACKET RATING: PVC, OFNR
 JACKET COLOR: SEE CHART, SHEET 2 OF 2
 CABLE O.D: 3.0 mm

TESTING:

DOUBLE ENDED INSERTION LOSS TEST.
 CABLES WITH GREATER THAN 1.0 dB OF LOSS ARE REJECTED.

CONNECTOR POLISH: THIS ASSEMBLY UTILIZES A PC POLISH.

MISCELLANEOUS:

OPERATING TEMPERATURE: -20° C TO +70° C.
 CABLE ASSEMBLY TO BE PACKAGED WITH DUST CAPS INSTALLED. (NOT SHOWN).
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:


CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	11/12/07			
	CHECKED BY D.PARHAM	11/12/07	CATEGORY	FIBER OPTICS	
	APPROVED BY P.McNEIL	11/12/07	PRODUCT DESCRIPTION	9/125 SC-SC DPLX ASSY	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. SFODSC-COLOR	REV. B
REF	SCALE: NONE	CAD FILE: SFODSC-COLOR.SLDDRW	SHEET 1 OF 2		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NO.	JACKET COLOR	LENGTH METER [FT]
SFODSC-RD-01	RED	1 [3.28]
SFODSC-RD-02	RED	2 [6.56]
SFODSC-RD-03	RED	3 [9.84]
SFODSC-RD-04	RED	4 [13.12]
SFODSC-RD-05	RED	5 [16.40]
SFODSC-RD-10	RED	10 [32.81]
SFODSC-RD-15	RED	15 [49.22]
SFODSC-GR-01	GREEN	1 [3.28]
SFODSC-GR-02	GREEN	2 [6.56]
SFODSC-GR-03	GREEN	3 [9.84]
SFODSC-GR-04	GREEN	4 [13.12]
SFODSC-GR-05	GREEN	5 [16.40]
SFODSC-GR-10	GREEN	10 [32.81]
SFODSC-GR-15	GREEN	15 [49.22]
SFODSC-BL-01	BLUE	1 [3.28]
SFODSC-BL-02	BLUE	2 [6.56]
SFODSC-BL-03	BLUE	3 [9.84]
SFODSC-BL-04	BLUE	4 [13.12]
SFODSC-BL-05	BLUE	5 [16.40]
SFODSC-BL-10	BLUE	10 [32.81]
SFODSC-BL-15	BLUE	15 [49.22]
SFODSC-OR-01	ORANGE	1 [3.28]
SFODSC-OR-02	ORANGE	2 [6.56]
SFODSC-OR-03	ORANGE	3 [9.84]
SFODSC-OR-04	ORANGE	4 [13.12]
SFODSC-OR-05	ORANGE	5 [16.40]
SFODSC-OR-10	ORANGE	10 [32.81]
SFODSC-OR-15	ORANGE	15 [49.22]

△ B

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY <p style="text-align: center;">FIBER OPTICS</p>			
PRODUCT DESCRIPTION <p style="text-align: center;">9/125 SC-SC DPLX ASSY</p>			
SIZE A	FSCM NO. 43321	DWG. NO. SFODSC-COLOR	REV. B
SCALE: NONE		CAD FILE: SFODSC-COLOR.SLDDRW	
			SHEET 2 OF 2