


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|--------------------------------|----------|--------------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | DRAWING REPLACES SFODST-01-OD1 | 10/17/14 | D. DESJARDIN |
| | | | |
| | | | |



| PART NUMBER | METERS [FEET] |
|-------------|---------------|
| SFODST-01 | 1.0 [3.28] |
| SFODST-02 | 2.0 [6.56] |
| SFODST-03 | 3.0 [9.84] |
| SFODST-04 | 4.0 [13.12] |
| SFODST-05 | 5.0 [16.40] |

NOTES:

1. ST CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

| | | | | |
|---|--|----------|---------------------------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% | APPROVALS | DATE | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | DRAWN BY MCCORMICK | 01/02/01 | | CATEGORY |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13] | CHECKED BY D.PARHAM | 01/02/01 | PRODUCT DESCRIPTION | |
| PROJECTION | APPROVED BY R.CARRICK | 01/02/01 | CA ST-ST 9/125 DUPLEX | |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | SIZE A | FSCM NO. 43321 |
| | COLOR VARIATIONS MAY OCCUR | | DWG. NO. SFODST | REV. A |
| | | | SCALE: NONE | CAD FILE: SFODST.SLDDRW |
| | | | | SHEET 1 OF 1 |