


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/07	D.FRISIELLO
B	ECN 7306: ADD COLOR ORANGE, SHEET 2, REVISE ROHS NOTE, FORMAT	2/24/14	D.FRISIELLO



NOTES:

CABLE CHARACTERISTICS:
 9/125 SINGLE MODE DUPLEX FIBER ZIPCORD.
 JACKET RATING: PVC, OFNR.
 JACKET COLOR: SEE CHART, SHEET 2 OF 2.
 CABLE O.D: 3.0 mm.

TESTING:
 BACK REFLECTION TESTED AT 1310 nm WITH A < -40dB RESULT.

CONNECTOR POLISH: THIS ASSEMBLY UTILIZES A PC POLISH.

MISCELLANEOUS:
 OPERATING TEMPERATURE: -20° C TO +70° C.
 CABLE ASSEMBLY TO SHIP WITH DUST CAPS INSTALLED. (NOT SHOWN).
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	11/12/07		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY D.PARHAM	11/12/07	CATEGORY FIBER OPTICS	
	APPROVED BY P.McNEIL	11/12/07	PRODUCT DESCRIPTION ST-ST DPLX ASSEMBLY	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
REF	SCALE: NONE	CAD FILE: SFODST-COLOR.SLDDRW	DWG. NO. SFODST-COLOR	REV. B

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NO.	JACKET COLOR	LENGTH MTR [FT]
SFODST-RD-01	RED	1 M [3.28 FT]
SFODST-RD-02	RED	2 M [6.56 FT]
SFODST-RD-03	RED	3 M [9.84 FT]
SFODST-RD-04	RED	4 M [13.12 FT]
SFODST-RD-05	RED	5 M [16.40 FT]
SFODST-RD-10	RED	10 M [32.81 FT]
SFODST-RD-15	RED	15 M [49.22 FT]
SFODST-GR-01	GREEN	1 M [3.28 FT]
SFODST-GR-02	GREEN	2 M [6.56 FT]
SFODST-GR-03	GREEN	3 M [9.84 FT]
SFODST-GR-04	GREEN	4 M [13.12 FT]
SFODST-GR-05	GREEN	5 M [16.40 FT]
SFODST-GR-10	GREEN	10 M [32.81 FT]
SFODST-GR-15	GREEN	15 M [49.22 FT]
SFODST-BL-01	BLUE	1 M [3.28 FT]
SFODST-BL-02	BLUE	2 M [6.56 FT]
SFODST-BL-03	BLUE	3 M [9.84 FT]
SFODST-BL-04	BLUE	4 M [13.12 FT]
SFODST-BL-05	BLUE	5 M [16.40 FT]
SFODST-BL-10	BLUE	10 M [32.81 FT]
SFODST-BL-15	BLUE	15 M [49.22 FT]
SFODST-OR-01	ORANGE	1 M [3.28 FT]
SFODST-OR-02	ORANGE	2 M [6.56 FT]
SFODST-OR-03	ORANGE	3 M [9.84 FT]
SFODST-OR-04	ORANGE	4 M [13.12 FT]
SFODST-OR-05	ORANGE	5 M [16.40 FT]
SFODST-OR-10	ORANGE	10 M [32.81 FT]
SFODST-OR-15	ORANGE	15 M [49.22 FT]

B

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY			
FIBER OPTICS			
PRODUCT DESCRIPTION			
ST-ST DPLX ASSEMBLY			
SIZE	FSCM NO.	DWG. NO.	REV.
A	43321	SFODST-COLOR	B
SCALE: NONE		CAD FILE: SFODST-COLOR.SLDDRW	SHEET 2 OF 2