


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REPLACES SF0ST-LC-01-OD1	6/24/14	D. CASTRO



PART NUMBER	LENGTH	
	METERS	[FEET]
SF0ST-LC-01	1.0	[3.3]
SF0ST-LC-02	2.0	[6.6]
SF0ST-LC-03	3.0	[9.8]
SF0ST-LC-04	4.0	[13.1]
SF0ST-LC-05	5.0	[16.4]

**NOTES:**

1. ST CONNECTOR ASSEMBLY POLISH TYPE: PC  
LC CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	APPROVALS DRAWN BY C.McCORMICK	DATE 01/02/01		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CHECKED BY DFP	DATE 01/19/01		CATEGORY FIBER OPTICS		
	APPROVED BY R.CARRICK	DATE 01/19/01	PRODUCT DESCRIPTION CA ST-LC 9/125 SIMPLEX			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. SF0ST-LC

SCALE: NONE | CAD FILE: SF0ST-LC.SLDDRW | SHEET 1 OF 1