


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REPLACES SFOST-SC-01-OD1	6/24/14	D. CASTRO





PART NUMBER	LENGTH	
	METERS	[FEET]
SFOST-SC-01	1.0	[3.3]
SFOST-SC-02	2.0	[6.6]
SFOST-SC-03	3.0	[9.8]
SFOST-SC-04	4.0	[13.1]
SFOST-SC-05	5.0	[16.4]

**NOTES:**

1. ST CONNECTOR ASSEMBLY POLISH TYPE: PC  
SC CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY C.McCORMICK	12/28/00		CATEGORY <b>FIBER OPTICS</b>		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY DFP	01/22/01	PRODUCT DESCRIPTION <b>CA ST-SC 9/125 SIMPLEX</b>			
	APPROVED BY R.CARRICK	01/22/01		<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>FSCM NO. <b>43321</b></td> <td>DWG. NO. <b>SFOST-SC</b></td> <td>REV. <b>A</b></td> </tr> </table>	SIZE <b>A</b>	FSCM NO. <b>43321</b>
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>SFOST-SC</b>	REV. <b>A</b>			
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: SFOST-SC.SLDDRW			
			SHEET 1 OF 1			