


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	DRAWING REPLACES SPV332-38-OD1 AT REV A	12/17/14	D.FRISIELLO



SPECIFICATIONS:

GENERAL PURPOSE, IRRADIATED POLYOLEFIN
 FIT@-221= 2:1 SHRINK RATIO
 MIL-DTL-23053/5C,
 CLASS 1, 2
 UL STANDARD 224
 CSA STANDARD 198
 COLOR; BLACK

PACKAGING:
 100 PIECES PER BAG.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $>12 [305] - 60 [1524] = +2 [51] / -0$ $>60 [1524] - 120 [3048] = +4 [102] / -0$ $>120 [3048] - 300 [7620] = +6 [152] / -0$ $>300 [7620] = +5\% / -0\%$ ALL OTHER DIMENSIONAL TOLERANCES: $.X = .2 [5.08]$ $.XX = .02 [51]$ $.XXX = .005 [13]$	APPROVALS DRAWN BY R.CARRICK CHECKED BY ENG APPROVED BY C.MCCORMICK	DATE 8/12/2004 8/12/2004 8/12/2004			45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY D-SUBMINIATURE	PRODUCT DESCRIPTION SHRINK, 3/32"ODX3/8"L 100/PK	
	SIZE A	FSCM NO. 43321	DWG. NO. SPV332-38	REV. A	SCALE: 8:1 CAD FILE: SPV332-38.SLDDRW SHEET 1 OF 1