


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/15/2020	PHOSPODAR



PARAMETER	SPECIFICATION
FIBER TYPE	OM4
CONNECTOR TYPE	LC/UPC
ADAPTER TYPE	LC ADAPTER, AQUA

ITEM NUMBER	SPLIT	WAVELENGTHS	INSERTION LOSS PER SPLIT	PDL	RETURN LOSS	DIRECTIVITY
		nm	dB	dB	dB	dB
TAP-LCM4-5050-LGX	50/50	850±20	3.9/3.9	≤ 0.15	≥ 50	≥ 55
TAP-LCM4-6040-LGX	60/40		2.9/4.9			
TAP-LCM4-7030-LGX	70/30		2.2/6.2			
TAP-LCM4-9802-LGX	98/2		0.5/19.1			

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY: DZINN CHECKED BY: BPUCHASKI APPROVED BY: PHOSPODAR	DATE 06/15/2020 06/15/2020 06/15/2020	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 		
PRODUCT DESCRIPTION PASSIVE OPTICAL TAP, MMF OM4 LC CONNECTORS			SCALE: NONE CAD FILE: TAP-LCM4-xxxx-LGX.SLDDRW SHEET 1 OF 1
COLOR VARIATIONS MAY OCCUR		SIZE: A	CAGE CODE: 43321 ITEM NO.: TAP-LCM4-xxxx-LGX