


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/2020	PHOSPODAR



ITEM NUMBER	SPLIT	WAVELENGTHS	INSERTION LOSS PER SPLIT	PDL	RETURN LOSS
		nm	dB	dB	dB
TAP-PTSM-5050-F	50/50	1310±10 1550±10	3.8	≤ 0.15	≥ -55
TAP-PTSM-6040-F	60/40		2.9/5.0		
TAP-PTSM-7030-F	70/30		2.2/6.4		
TAP-PTSM-8020-F	80/20		1.4/8.5		
TAP-PTSM-9010-F	90/10		0.8/12.7		

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]</p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DFRISIELLO	11/12/2020			
	CHECKED BY PHOSPODAR	11/12/2020	CATEGORY	FIBER OPTIC	
	APPROVED BY PHOSPODAR	11/12/2020	PRODUCT DESCRIPTION	Passive Optical Tap, SMF no connectors	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. TAP-PTSM-xxxx-F	REV. A
		SCALE: NONE	CAD FILE: TAP-PTSM-xxxx-F.SLDDRW	SHEET 1 OF 1	