


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |            |             |
|-----------|-----------------|------------|-------------|
| REV       | DESCRIPTION     | DATE       | APPROVED    |
| A         | INITIAL RELEASE | 01/21/2022 | GUTTA DAURO |
|           |                 |            |             |
|           |                 |            |             |




USB 3.2  
 8 PAIR, INDIVIDUALLY SHIELDED, 30AWG STRANDED TINNED COPPER  
 4 COND. 32AWG STRANDED TINNED COPPER  
 1 COND. 32AWG STRANDED TINNED COPPER  
 2X 34AWG TINNED COPPER SHIELD  
 1X 22AWG TINNED COPPER SHIELD  
 3X DRAIN WIRE  
 JACKET: TPE, BLACK

| ITEM NUMBER    | LENGTH MM [FT]     |
|----------------|--------------------|
| TB4P-MM-BLK-1F | 304.8 +51/-0 [1.0] |
| TB4P-MM-BLK-2F | 609.6 +51/-0 [2.0] |
| TB4P-MM-BLK-3F | 914.4 +51/-0 [3.0] |

**NOTES:**

- VOLTAGE TEST: DC 300V 10MS  
 INSULATION RESISTANCE: 5.0M ohm/min.  
 CONDUCTANCE RESISTANCE: 5.0 ohm/max.  
 SUPPORT: 20V@5A CHARGE; DATA TRANSMISSION: 40Gbp/s 8K/60Hz
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

**REGULATORY COMPLIANCE:**  
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

|  |  |  |   |
|--|--|--|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]   FRACTIONS ± 1/32<br>.XX = ± .02 [5]   ANGLES ± 1°<br>.XXX = ± .005 [13] | APPROVALS<br>DRAWN BY DFRISIELLO<br>CHECKED BY DGUST<br>APPROVED BY GUTTA DAURO        | DATE<br>01/21/2022<br>01/21/2022<br>01/21/2022 | <br>an INFINITO brand<br>50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |
|  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY<br>COLOR VARIATIONS MAY OCCUR | CATEGORY<br><b>AUDIO/VIDEO</b>                 | PRODUCT DESCRIPTION<br><b>Thunderbolt 4 Compatible, C-M/C-M, TPE, BLK</b>   |