

Bulk Cable Specification

TC2382 Category 5e Cable

Cross-Sectional View		Color Code
		Pair 1. Blue, White/Blue
		Pair 2. Orange, White/Orange
		Pair 3. Green, White/Green
		Pair 4. Brown, White/Brown
ITEM		DESCRIPTION
Conductor	No. of Conductors	4 Pairs
	Material	Tinned copper
	Construction	24 AWG Stranded (7/32)
Insulation	Material	Polyethylene
Jacket	Material	PVC
	Nominal Thickness	.021"
	Nominal Diameter	.215"
	Color	Beige
Marking:		
ELECTRICAL PROPERTIES		
Conductor Resistance	26.0 Ohms/1000 feet	
Conductor to conductor capacitance	13.5pF/ft	
Impedance	100 Ohms	
LISTINGS / RATINGS		
NEC type CM, Article 800		
CEC type CMG		