


Bulk Cable Specification

TC25XX Category 5e Cable

<p>Cross-Sectional View</p>  <p>JACKET</p> <p>TWISTED PAIR</p>		<p>Color Code</p> <p>Pair 1. Blue, White/Blue Pair 2. Orange, White/Orange Pair 3. Green, White/Green Pair 4. Brown, White/Brown</p>
ITEM		DESCRIPTION
Conductor	No. of Conductors	4 Pairs
	Material	Tinned Copper
	Construction	24 AWG Stranded (7/32)
Insulation	Material	Polyethylene
Jacket	Material	PVC
	Nominal Thickness	.020"
	Nominal Diameter	.213"
	Color	See Table
<p>Jacket Marking: QUABBIN DATAMAX 5E 350 MHZ ISO 11801 PATCH CORD P/N (QUABBIN P/N) – (UL) TYPE CMR 24 AWG 75C – CSA LL51726 TYPE CMG 60C – ETL VERIF. TIA-568-C.2 CAT 5e – RoHS – (LOT DESIGNATOR) (SEQUENTIAL FOOTAGE)</p>		
ELECTRICAL PROPERTIES		
Conductor Resistance		26.0 Ohms/1000 feet
Conductor to conductor capacitance		13.5pF/ft
Impedance		100 Ohms
LISTINGS / RATINGS		
NEC type CM, Article 800		
CEC type CMG		

PART NUMBER	CABLE JACKET COLOR
TC2581-CS1	YELLOW
TC2589-CS1	RED
TC2590-CS1	GREEN
TC2591-CS1	BLACK
TC2592-CS1	VIOLET
TC2593-CS1	WHITE
TC2594-CS1	ORANGE
TC2599-CS1	BLUE