


Bulk Cable Specification

<p>Cross-Sectional View</p> 		<p>Color Code</p> <ol style="list-style-type: none"> 1. Violet (Pink) 2. Gray (Slate) 3. Orange 4. Black 5. Red 6. Green 7. Yellow 8. Blue 9. Brown 10. White
ITEM		DESCRIPTION
Conductor	No. of Conductors	10
	Material	Bare Copper
	Construction	26 AWG Stranded (7x34)
Insulation	Material	Polypropylene
	Nominal Diameter	0.038" [0.97mm]
	Thickness	0.005" [0.13mm] Minimum
Shielding	Material	N/A
	Coverage	N/A
Drain Wire	Material	N/A
	Construction	N/A
Braiding	Material	N/A
	Coverage	N/A
Jacket	Material	PVC
	Thickness	0.016" [0.41mm] Minimum
	Nominal Diameter	Oval
	Color	Silver Satin
ELECTRICAL PROPERTIES		
Conductor Resistance		N/A
Insulation Resistance		N/A
Impedance		N/A
Maximum Voltage		150V
Maximum Current Rating		N/A
LISTINGS / RATINGS		
RoHS Compliant		Yes
Flammability Rating		VW-1
UL Style		20251
MISCELLANEOUS		
Operating Temperature		+60°C Maximum
Minimum Bending Radius		N/A
Packaging		1000 FT: Spool with Stretch Wrap