


**Bulk Cable Specification**

<p>RCross-Sectional View</p> 		<p>Color Code</p> <ol style="list-style-type: none"> <li>1. White (Gray)</li> <li>2. Orange</li> <li>3. Black</li> <li>4. Red</li> <li>5. Green</li> <li>6. Yellow</li> <li>7. Blue</li> <li>8. Brown</li> </ol>
ITEM		DESCRIPTION
Conductor	No. of Conductors	8
	Material	Bare Copper
	Construction	26 AWG Stranded (7x34)
Insulation	Material	Polypropylene
	Nominal Diameter	0.038" [0.97mm]
	Thickness	0.005" [0.13mm] Minimum
Shielding	Material	N/A
	Coverage	N/A
Drain Wire	Material	N/A
	Construction	N/A
Braiding	Material	N/A
	Coverage	N/A
Jacket	Material	PVC
	Thickness	0.016" [0.41mm] Minimum
	Nominal Diameter	Oval
	Color	Silver Satin
ELECTRICAL PROPERTIES		
Conductor Resistance	N/A	
Insulation Resistance	N/A	
Impedance	N/A	
Maximum Voltage	150V	
Maximum Current Rating	N/A	
LISTINGS / RATINGS		
RoHS Compliant	Yes	
Flammability Rating	VW-1	
UL Style	20251	
MISCELLANEOUS		
Operating Temperature	+60°C Maximum	
Minimum Bending Radius	N/A	
Packaging	100 FT: Coil with Stretch Wrap in accordance with L-com specification PS-0031 500 FT: Reel with Stretch Wrap 1000 FT: Reel with Stretch Wrap	