


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
G	ECN6669: CN RELEASE. UPD FORMAT/PKG.	8/27/13	D_DESJARDIN
H	ECN 7055: CATEGORY 3 CABLE NOTE WAS CATEGORY 5E	9/11/13	D_DESJARDIN
J	ECN 7141: REVISED OVERALL LENGTH FROM CL/CL TO END/ END, ROHS	11/6/13	D.FRISIELLO



PART NUMBER	LENGTH FEET [METERS]
TDC350FF-5	5.0 [1.52]
TDC350FF-10	10.0 [3.05]
TDC350FF-15	15.0 [4.57]
TDC350FF-25	25.0 [7.62]
TDC350FF-50	50.0 [15.24]
TDC350FF-100	100.0 [30.48]



NOTES:

- SEE SHEET 2 FOR WIRING MAP.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY ENG APPROVED BY R.CARRICK	DATE 09/21/2001 09/21/2001 09/21/2001			45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR		
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION CABLE CAT 3 CN50 F/F		
	PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. TDC350FF	REV. J

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

WIRING MAP

PAIR	"J1"	COLOR	"J2"	PAIR	"J1"	COLOR	"J2"
1	1	BLUE/WHITE	1	14	14	BROWN/BLACK	14
	26	WHITE/BLUE	26		39	BLACK/BROWN	39
2	2	ORANGE/WHITE	2	15	15	GRAY/BLACK	15
	27	WHITE/ORANGE	27		40	BLACK/GRAY	40
3	3	GREEN/WHITE	3	16	16	BLUE/YELLOW	16
	28	WHITE/GREEN	28		41	YELLOW/BLUE	41
4	4	BROWN/WHITE	4	17	17	ORANGE/YELLOW	17
	29	WHITE/BROWN	29		42	YELLOW/ORANGE	42
5	5	GRAY/WHITE	5	18	18	GREEN/YELLOW	18
	30	WHITE/GRAY	30		43	YELLOW/GREEN	43
6	6	BLUE/RED	6	19	19	BROWN/YELLOW	19
	31	RED/BLUE	31		44	YELLOW/BROWN	44
7	7	ORANGE/RED	7	20	20	GRAY/YELLOW	20
	32	RED/ORANGE	32		45	YELLOW/GRAY	45
8	8	GREEN/RED	8	21	21	BLUE/VIOLET	21
	33	RED/GREEN	33		46	VIOLET/BLUE	46
9	9	BROWN/RED	9	22	22	ORANGE/VIOLET	22
	34	RED/BROWN	34		47	VIOLET/ORANGE	47
10	10	GRAY/RED	10	23	23	GREEN/VIOLET	23
	35	RED/GRAY	35		48	VIOLET/GREEN	48
11	11	BLUE/BLACK	11	24	24	BROWN/VIOLET	24
	36	BLACK/BLUE	36		49	VIOLET/BROWN	49
12	12	ORANGE/BLACK	12	25	25	GRAY/VIOLET	25
	37	BLACK/ORANGE	37		50	VIOLET/GRAY	50
13	13	GREEN/BLACK	13				
	38	BLACK/GREEN	38				

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
CABLE CAT 3 CN50 F/F			
SIZE	FSCM NO.	DWG. NO.	REV.
A	43321	TDC350FF	J
SCALE: NONE		CAD FILE: TDC350FF.SLDDRW	SHEET 2 OF 2