


Bulk Cable Specification

TFC2070 Category 5e Cable

Cross-Sectional View 		Color Code Pair 1. Blue, White/Blue Pair 2. Orange, White/Orange Pair 3. Green, White/Green Pair 4. Brown, White/Brown
ITEM		DESCRIPTION
Conductor	No. of Conductors	4 Pairs
	Material	Bare copper
	Construction	24 AWG Solid
Insulation	Material	Polyethylene
Shielding	Material	Aluminum / polyester tape
	Coverage	100%
Drain Wire	Material	Tinned copper
	Construction	24 AWG Solid
Jacket	Material	PVC
	Rating	Riser
	Nominal Diameter	.223 in
	Color	Blue
Marking:		
ELECTRICAL PROPERTIES		
Conductor Resistance		9.8 Ω /100 m
Mutual Capacitance		14 pF/ft at 1 MHz
Impedance		100±15 Ω 1-100MHz
LISTINGS / RATINGS		
UL Type CMR or CMP		
RoHS compliant		
Temperature Rating: -10° C to +75° C		