


Bulk Cable Specification

TFC6018 CATEGORY 6A RISER



| ITEM | DESCRIPTION | |
|--|-------------------|---------------------------------------|
| Conductor | No. of Conductors | 4 Twisted Pairs |
| | Material | Solid Bare Copper |
| | Construction | 23 AWG |
| Insulation | Material | Polyethylene |
| Shielding | Material | Aluminum/Polyester (Aluminum Side In) |
| | Coverage | 100% |
| Drain Wire | Material | Tinned copper |
| | Construction | 24 AWG |
| Jacket | Material | PVC Flame Retardant |
| | Nominal Diameter | .295" |
| | Color | BLUE TFC6018 WHITE TFC6019 |
| Jacket Marking: COMTRAN CABLE LLC COM-Link CAT 6A 500MHz 23 AWG SHIELDED CMR C(UL)US ETL VERIFIED TO ANSI/TIA-568-C.2 CATEGORY 6A RoHS (01-12345) 0/1000 | | |
| ELECTRICAL PROPERTIES | | |
| DC Resistance, MAX | 9.38 Ω / 100 m | |
| Impedance | 100 ±15 Ω | |
| Voltage Rating, MAX | 300 V | |
| LISTINGS / RATINGS | | |
| Temperature Rating: -20°C to + 75°C | | |
| RoHS COMPLIANT, UL 1666 Riser Flame Test, UL listed type CMR, ETL Verified ANSI/TIA-568-C.2 Cat 6A | | |
| PACKAGING | | |
| 1000K FOOT REEL | | |

01/29/15(Information subject to change without notice)