



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
L	ECN 10346: ADDED -100, -500, NEW FORMAT	01/29/2020	GUTTADAURO

TFC6101-XXX CONSISTS OF A CONTINUOUS LENGTH OF BULK CABLE



COLOR CODE  
 BLUE x WHITE/BLUE  
 ORANGE x WHITE/ORANGE  
 GREEN x WHITE/GREEN  
 BROWN x WHITE/BROWN



NOTES:

- CONSTRUCTION:  
 CONDUCTOR: 26 AWG STRANDED TINNED COPPER  
 INSULATION MATERIAL: POLYOLEFIN  
 PAIRS: COLOR CODED SINGLES TWISTED INTO PAIRS  
 SPLINE: POLYTETHYLENE  
 SHIELD: AN ALUMINUM POLYESTER FOIL SHIELD, 100% COVERAGE  
 DRAIN WIRE: TINNED COPPER, 26AWG  
 JACKET: PVC
- PHYSICAL PROPERTIES:  
 TEMPERATURE RATING: -20° C TO +75° C  
 MINIMUM BEND RADIUS: 1.0" (STATIC BEND)
- AGENCY APPROVALS:  
 NEC (UL) TYPE CMR/CMG; CEC (UL) TYPE CMR/CMG, RoHS COMPLIANT
- JACKET PRINT:  
 L-COM, INC CATEGORY 6 F/UTP 100 OHM PATCH CORD TFC6101 - PVC -- RoHS -- (LOT DESIGNATOR)(SEQUENTIAL FOOTAGE)
- ELECTRICAL CHARACTERISTICS:  
 CONDUCTOR RESISTANCE, MAX. 14.0 OHM/100 METERS  
 IMPEDANCE 100 +/- 15 OHM 1-250 MHZ

O.D: .036"

CABLE DIA: .235" (.240" MAX.)

MODEL NUMBER	LENGTH	COLOR	PACKAGING
TFC6101	1000.0 FT	LIGHT GRAY (RAL7035)	SPOOL
TFC6101-100	100.0 FT	LIGHT GRAY (RAL7035)	POLY BAG
TFC6101-500	500.0 FT	LIGHT GRAY (RAL7035)	SPOOL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [51] .XXX = .005 [13]	APPROVALS	DATE	 an INFINIT® brand 50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY DFRISIELLO	01/20/2020	
	CHECKED BY GUTTADAURO	01/29/2020	PRODUCT DESCRIPTION C6 F/UTP 26STR PVC CMR GRY
	APPROVED BY GUTTADAURO	01/29/2020	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR
PROJECTION		SIZE <b>A</b>	FSCM NO. <b>43321</b> DWG. NO. <b>TFC6101</b>
		SCALE: NONE	CAD FILE: TFC6101.SLDDRW SHEET 1 OF 1