


**Bulk Cable Specification**

**TFPC6021 CATEGORY 6A PLENUM**



ITEM	DESCRIPTION	
Conductor	No. of Conductors	4 Twisted Pairs
	Material	Solid Bare Copper
	Construction	23 AWG
Insulation	Material	FEP
Shielding	Material	Aluminum/Polyester (Aluminum Side In)
	Coverage	100%
Drain Wire	Material	Tinned copper
	Construction	24 AWG
Jacket	Material	Low-Smoke PVC
	Nominal Diameter	.295"
	Color	BLUE TFPC6021 WHITE TFPC6022 GRAY TFPC6023

△<sub>B</sub> Jacket Marking: COMTRAN CABLE LLC COM-Link CAT 6A 500 MHz 23 AWG SHIELDED CMP C(UL)US ETL VERIFIED TO ANSI/TIA-568-C.2 CATEGORY 6A RoHS (01-12345) 0/1000

**ELECTRICAL PROPERTIES**

DC Resistance, MAX	9.38 Ω / 100 m
Impedance	100 ±15 Ω
Voltage Rating, MAX	300 V

**LISTINGS / RATINGS**

Temperature Rating: -20°C to + 75°C  
 RoHS COMPLIANT, NFPA 262, (UL 910) Plenum Flame Test, UL listed type CMP, ETL Verified  
 ANSI/TIA-568-C.2 Cat 6A

**PACKAGING**

△<sub>B</sub> 1000 FOOT REEL

(Information subject to change without notice)