



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
K	ECN 10346: ADDED -100, -500, NEW FORMAT	01/29/2020	GUTTADAURO

TFSC2004-XXX CONSISTS OF A CONTINUOUS LENGTH OF BULK CABLE



COLOR CODE
 BLUE x WHITE/BLUE
 ORANGE x WHITE/ORANGE
 GREEN x WHITE/GREEN
 BROWN x WHITE/BROWN

NOTES:

- CONSTRUCTION:**
 CONDUCTOR: 24 AWG SOLID BARE COPPER
 INSULATION MATERIAL: POLYOLEFIN
 PAIRS: COLOR CODED SINGLES TWISTED INTO PAIRS
 BINDER: MYLAR TAPE, 100% COVERAGE WITH 25% OVERLAPPING
 SHIELD: AN ALUMINUM POLYESTER FOIL SHIELD, 100% COVERAGE (FOIL IN) WITH 25% OVERLAPPING
 OUTER BRAID: TIN PLATED COPPER, 60% COVERAGE, MIN.
 DRAIN WIRE: 24 AWG STRANDED TINNED COPPER
 JACKET: POLYVINYLCHELORIDE, GRAY (RAL 7044)
 O.D: .043" ± .002" [1.09mm +/-0.05mm]
 NOMINAL DIA: 0.256" +/- .006 [6.5mm +/- .15mm]
- PHYSICAL PROPERTIES:**
 TEMPERATURE RATING: -20 ° C TO +80 ° C
- AGENCY APPROVALS:** CATEGORY 5E, RoHS COMPLIANT
- JACKET PRINT:**
 L-COM, INC WWW.L-COM.COM VERIFIED TO TIA/EIA-568-B.2 CAT 5e 24AWG PVC SF/UTP ROHS WW/YY
- ELECTRICAL CHARACTERISTICS:**
 DIELECTRIC STRENGTH: 500V AC/1 MIN.
 INSULATION RESISTANCE: MIN. 100 MEGA OHMS - 10m @20 ° C
 CONDUCTOR RESISTANCE: MAX 93.8 OHMS/km AT 20 ° C

MODEL NUMBER	LENGTH	COLOR	PACKAGING
TFSC2004	1000.0 FT	GRAY (RAL7044)	SPOOL
TFSC2004-100	100.0 FT	GRAY (RAL7044)	POLY BAG
TFSC2004-500	500.0 FT	GRAY (RAL7044)	SPOOL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [51] .XXX = .005 [13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY GUTTADAURO APPROVED BY GUTTADAURO	DATE 01/21/2020 01/29/2020 01/29/2020		50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR	PRODUCT DESCRIPTION C5E SFTP 4PR/24 SLD PVC GRY
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TFSC2004	REV. K
		SCALE: NONE	CAD FILE: TFSC2004.SLDDRW	SHEET 1 OF 1	