


Bulk Cable Specification

TPC2567 Category 5e Cable

<p>Cross-Sectional View</p> 		<p>Color Code</p> <p>Pair 1. Blue, White/Blue</p> <p>Pair 2. Orange, White/Orange</p> <p>Pair 3. Green, White/Green</p> <p>Pair 4. Brown, White/Brown</p>
ITEM		DESCRIPTION
Conductor	No. of Conductors	4 Pairs
	Material	Solid bare copper
	Construction	24 AWG solid
Insulation	Material	Fluoropolymer
Jacket	Material	Plenum PVC
	Nominal Diameter	.168"
	Color	Blue
Marking:		
ELECTRICAL PROPERTIES		
Conductor DC Resistance		9.38/100 meters Max
Mutual Capacitance		14pF/ft Nominal
Impedance		100 Ω ± 15%
LISTINGS / RATINGS		
UL, c(UL) Type CMP		
ETL Verified to Category 5e Enhanced (Tested to 350 MHz)		
RoHS Compliant		
Operating Temperature: -10 to 75°C		
PACKAGING		
1000 ft Pull box		