


**Bulk Cable Specification**

**TPC4757 Category 3 Cable**

<p>Cross-Sectional View</p>  <p>JACKET RIPCORD TWISTED PAIR</p>		<p>Color Code</p> <p>Pair 1. Blue, White/Blue</p> <p>Pair 2. Orange, White/Orange</p> <p>Pair 3. Green, White/Green</p>
ITEM		DESCRIPTION
Conductor	No. of Conductors	3 Pairs
	Material	24 AWG Solid Bare Copper
Insulation	Material	Plenum PVC
Jacket	Material	Plenum PVC
	Nominal Diameter	.143"
	Color	Green
<p>Marking: E106583 (01-12345) 24 AWG CMP C(UL)US - IEEE 802.3 10 BASE T ETL VERIFIED TO TIA-568-B.2 CAT 3 RoHS</p>		
<p><b>ELECTRICAL PROPERTIES</b></p>		
Conductor DC Resistance		27 Ω/Kft
Mutual Capacitance		17.5 pF/ft Nominal
Impedance		100 Ω ± 15%
<p><b>LISTINGS / RATINGS</b></p>		
UL, c(UL) Type CMP		
ETL Verified TO TIA-568-B.2 CAT 3		
RoHS Compliant		
Operating Temperature: -10 to 75°C		
<p><b>PACKAGING</b></p>		
1000 ft Pull Box		