


Bulk Cable Specification

TPC5012 Category 5e Cable

Cross-Sectional View		Color Code
		Pair 1. Blue, Blue / White Pair 2. Orange, Orange / White Pair 3. Green, Green / White Pair 4. Brown, Brown / White
ITEM		DESCRIPTION
Conductor	No. of Conductors	4 Pairs
	Material	Bare copper
	Construction	24 AWG solid
Insulation	Material	FEP
Jacket	Material	Low Smoke, flame retardant thermoplastic
	Nominal Diameter	.180"
	Color	Black
Marking:		
ELECTRICAL PROPERTIES		
Maximum Resistance Unbalance		5%
Maximum Capacitance Unbalance		330 pF/100 meters
Impedance		100 Ohms
Maximum Delay Skew		45 ns/100 meters
LISTINGS / RATINGS		
CMP		
CSA Type FT6		