


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/23/18	D.FRISIELLO
B	ECN 10610 CLARIFY BURN RATING ON CERTS	08/28/20	DGUTTADAURO



2X RJ45 (8P8C) SHIELDED PLUG

MODEL NUMBER	LENGTH FEET [METERS]
TRA6261-1F	1.0 [.30]
TRA6261-2F	2.0 [.61]
TRA6261-3F	3.0 [.91]
TRA6261-5F	5.0 [1.52]
TRA6261-10F	10.0 [3.05]
TRA6261-15F	15.0 [4.57]
TRA6261-25F	25.0 [7.62]
TRA6261-50F	50.0 [15.24]
TRA6261-75F	75.0 [22.86]
TRA6261-100F	100.0 [30.48]
TRA6261-125F	125.0 [38.10]
TRA6261-150F	150.0 [45.72]

4TP, CAT 6a, 26AWG STRANDED SILVER PLATED COPPER WITH ALUM/POLY FOIL SHIELD AND ROUND TINNED PLATED COPPER BRAID, (85% MIN. COVERAGE). JACKET: FEP, BLUE
 OPERATING TEMPERATURE RANGE: -55 °C TO +150 °C
 NOM. DIA: .230" [5.84], MIN. BEND RAD: 1.15" [29.2]



NOTES: B

FIRE PROPERTIES FEP JACKET: (FST)
 WILL MEETS OR EXCEEDS THE APPLICABLE REQUIREMENTS OF FAR 25.869, FAR 25.853, ABD0031, AND D6-51377;
 SEPERATE TESTING AND QUALIFICATION MAT BE REQUIRED FOR YOUR APPLICATION AS CERTIFICATION AUTHORITY AND DOCUMENTATION DOES NOT RESIDE WITH L-COM.

- LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
- PLUG CONFORMS TO TIA-1096.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.GUTTADAURO APPROVED BY D.GUTTADAURO	DATE 2/22/18 2/23/18 2/23/18	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY TELECOM/MODULAR	
THIRD-ANGLE PROJECTION 	SIZE A CAGE CODE 43321 SCALE: NONE	DWG. NO. TRA6261 CAD FILE: TRA6261.SLDDRW	REV. B SHEET 1 OF 1