






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
B	ECN 11731: IN PRODUCT DESCRIPTION "CMR-CMX" WAS "PTLC-CMR"	03/10/2022	DGUTTADAURO



CAT 5e, 4 TWISTED PAIR, 24AWG SOLID 600V PoE, F/UTP FOIL SHIELDED, OUTDOOR INDUSTRIAL JACKET: CMR-CMX-2463 PVC, BLACK

MODEL NUMBER	LENGTH FEET [METERS]
TRD544OS-BLK-1F	1.0 [0.30]
TRD544OS-BLK-3F	3.0 [0.91]
TRD544OS-BLK-5F	5.0 [1.52]
TRD544OS-BLK-10F	10.0 [3.05]
TRD544OS-BLK-15F	15.0 [4.57]
TRD544OS-BLK-25F	25.0 [7.62]
TRD544OS-BLK-50F	50.0 [15.24]
TRD544OS-BLK-75F	75.0 [22.86]
TRD544OS-BLK-100F	100.0 [30.48]
TRD544OS-BLK-150F	150.0 [45.72]
TRD544OS-BLK-200F	200.0 [60.96]
TRD544OS-BLK-250F	250.0 [76.20]



NOTES:

CABLE CHARACTERISTICS:
 TEMPERATURE RATING: -20°C TO +75°C
 VOLTAGE RATING: 600 V
 FLAME RATING: CMX OUTDOOR - CMR
 UL AWM STYLE: 2463
 CABLE JACKET IS SUNLIGHT (UV) AND OIL RESISTANT.

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 an INFINIT® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	06/09/2021		
THIRD-ANGLE PROJECTION 	CHECKED BY DGUTTADAURO	6/10/21	PRODUCT DESCRIPTION C5e F/UTP 24SLD 600V PoE CMR-CMX PVC BLK	
	APPROVED BY	6/10/21		
SIZE A CAGE CODE 43321 ITEM NO. TRD544OS-BLK		SCALE: NONE CAD FILE: TRD544OS-BLK.SLDDRW		REV. B