


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/23/2022	GUTTADAURO



**NOTES**


**MATERIAL:**  
 RJ45 MALE: POLYCARBONATE.  
 RJ45 FEMALE: ZINC ALLOY.  
 SHIELDS: NICKEL PLATE.  
 CONTACTS: COPPER ALLOY, GOLD PLATING: 50u".

**ELECTRICAL:**  
 NOMINAL VOLTAGE RATING: 30 V.  
 RESISTANCE: 15.2Ω/100m (MAXIMUM).  
 IMPEDANCE: 100Ω.  
 CAPACITANCE: 5600pf/100m.  
 PROPAGATION DELAY: 545ns/100m (MAXIMUM).  
 DELAY SKEW: 45ns/100m (MAXIMUM).  
 MAXIMUM POE RATING: IEEE 802.AT (PoE+).

**ENVIRONMENTAL:**  
 OPERATING TEMPERATURE RANGE: -20°C TO +60°C.

**MISCELLANEOUS**  
 CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY KGLEBOVA CHECKED BY DFRISIELLO APPROVED BY GUTTADAURO	DATE 6/16/2022 6/21/2022 6/23/2022	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				CATEGORY <b>TELECOM/MODULAR</b>
	THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>TRD626ADS-MPTL-10F</b>
	SCALE: NONE		CAD FILE: TRD626ADS-MPTL-10F.SLDDRW		SHEET 1 OF 1