

6

5

4

3

2

1

F

E



D

C

B

A

| REVISION |     |                 |            |            |            |
|----------|-----|-----------------|------------|------------|------------|
| ZONE     | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED   |
|          | A   | INITIAL RELEASE | 03/28/2024 | KGLEBOVA   | GUTTADAURO |



## NOTES:

1. LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

## REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

6


5

4

3

2

1

|                                                                                                                                                                                                               |           |                                                                                                                                                                       |           |                                                                                                                                                                        |        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|
| UNLESS OTHERWISE SPECIFIED<br>LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS                                                                                                              |           | <div>L-com®</div> <div>an INFINIT® brand</div> <div>Website: <a href="http://www.L-com.com">www.L-com.com</a></div> <div>Phone: 1.800.341.5266   1.978.682.6936</div> |           | <div></div> <div>INTERPRET ALL DIMENSIONS AND<br/>TOLERANCES PER ASME Y14.5</div> |        |
| TOLERANCES:                                                                                                                                                                                                   |           |                                                                                                                                                                       |           | SCALE                                                                                                                                                                  | SHEET  |
| X = ± .2 [5]<br>.XX = ± .02 [0.5]<br>.XXX = ± .005 [0.13]                                                                                                                                                     |           | FRACTIONS<br>± 1/32<br>ANGLES ± 1°                                                                                                                                    |           | NONE                                                                                                                                                                   | 1 OF 2 |
| CABLE LENGTH TOLERANCES:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤ 60 [1524] = +2 [51] / -0<br>>60 [1524] ≤ 120 [3048] = +4 [102] / -0<br>>120 [3048] ≤ 300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0 |           | DESCRIPTION<br><br>Cat6a FFTP RJ45 CMX LSZH 26AWG                                                                                                                     |           |                                                                                                                                                                        |        |
| ALL DIMENSIONS ARE FOR REFERENCE ONLY<br>AND SUBJECT TO CHANGE WITHOUT NOTICE.<br>UN-DIMENSIONED/NON-CRITICAL FEATURES<br>MAY VARY IN SIZE AND LOCATION<br>COLORS MAY VARY                                    |           |                                                                                                                                                                       |           |                                                                                                                                                                        |        |
| SIZE                                                                                                                                                                                                          | CAGE CODE | DRAWN BY                                                                                                                                                              | ITEM NO.  |                                                                                                                                                                        | REV    |
| A                                                                                                                                                                                                             | 43321     | KGLEBOVA                                                                                                                                                              | TRD626ASZ |                                                                                                                                                                        | A      |

6

5

4

3

2

1

F

E

D

C

B

A

F

E

D

C

B

A

| ITEM NO.           | COLOR | LENGTH |        |
|--------------------|-------|--------|--------|
|                    |       | FEET   | METERS |
| TRD626ASZ-BLK-1F   | BLACK | 1.0    | 0.30   |
| TRD626ASZ-BLK-2F   | BLACK | 2.0    | 0.61   |
| TRD626ASZ-BLK-3F   | BLACK | 3.0    | 0.91   |
| TRD626ASZ-BLK-5F   | BLACK | 5.0    | 1.52   |
| TRD626ASZ-BLK-7F   | BLACK | 7.0    | 2.13   |
| TRD626ASZ-BLK-10F  | BLACK | 10.0   | 3.05   |
| TRD626ASZ-BLK-15F  | BLACK | 15.0   | 4.57   |
| TRD626ASZ-BLK-25F  | BLACK | 25.0   | 6.10   |
| TRD626ASZ-BLK-50F  | BLACK | 50.0   | 7.62   |
| TRD626ASZ-BLK-75F  | BLACK | 75.0   | 9.14   |
| TRD626ASZ-BLK-100F | BLACK | 100.0  | 30.48  |


| ITEM NO.           | COLOR | LENGTH |        |
|--------------------|-------|--------|--------|
|                    |       | FEET   | METERS |
| TRD626ASZ-GRY-1F   | BLACK | 1.0    | 0.30   |
| TRD626ASZ-GRY-2F   | BLACK | 2.0    | 0.61   |
| TRD626ASZ-GRY-3F   | BLACK | 3.0    | 0.91   |
| TRD626ASZ-GRY-5F   | BLACK | 5.0    | 1.52   |
| TRD626ASZ-GRY-7F   | BLACK | 7.0    | 2.13   |
| TRD626ASZ-GRY-10F  | BLACK | 10.0   | 3.05   |
| TRD626ASZ-GRY-15F  | BLACK | 15.0   | 4.57   |
| TRD626ASZ-GRY-25F  | BLACK | 25.0   | 6.10   |
| TRD626ASZ-GRY-50F  | BLACK | 50.0   | 7.62   |
| TRD626ASZ-GRY-75F  | BLACK | 75.0   | 9.14   |
| TRD626ASZ-GRY-100F | BLACK | 100.0  | 30.48  |

| ITEM NO.           | COLOR | LENGTH |        |
|--------------------|-------|--------|--------|
|                    |       | FEET   | METERS |
| TRD626ASZ-BLU-1F   | BLUE  | 1.0    | 0.30   |
| TRD626ASZ-BLU-2F   | BLUE  | 2.0    | 0.61   |
| TRD626ASZ-BLU-3F   | BLUE  | 3.0    | 0.91   |
| TRD626ASZ-BLU-5F   | BLUE  | 5.0    | 1.52   |
| TRD626ASZ-BLU-7F   | BLUE  | 7.0    | 2.13   |
| TRD626ASZ-BLU-10F  | BLUE  | 10.0   | 3.05   |
| TRD626ASZ-BLU-15F  | BLUE  | 15.0   | 4.57   |
| TRD626ASZ-BLU-25F  | BLUE  | 25.0   | 6.10   |
| TRD626ASZ-BLU-50F  | BLUE  | 50.0   | 7.62   |
| TRD626ASZ-BLU-75F  | BLUE  | 75.0   | 9.14   |
| TRD626ASZ-BLU-100F | BLUE  | 100.0  | 30.48  |

| ITEM NO.           | COLOR | LENGTH |        |
|--------------------|-------|--------|--------|
|                    |       | FEET   | METERS |
| TRD626ASZ-RED-1F   | RED   | 1.0    | 0.30   |
| TRD626ASZ-RED-2F   | RED   | 2.0    | 0.61   |
| TRD626ASZ-RED-3F   | RED   | 3.0    | 0.91   |
| TRD626ASZ-RED-5F   | RED   | 5.0    | 1.52   |
| TRD626ASZ-RED-7F   | RED   | 7.0    | 2.13   |
| TRD626ASZ-RED-10F  | RED   | 10.0   | 3.05   |
| TRD626ASZ-RED-15F  | RED   | 15.0   | 4.57   |
| TRD626ASZ-RED-25F  | RED   | 25.0   | 6.10   |
| TRD626ASZ-RED-50F  | RED   | 50.0   | 7.62   |
| TRD626ASZ-RED-75F  | RED   | 75.0   | 9.14   |
| TRD626ASZ-RED-100F | RED   | 100.0  | 30.48  |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

|                                                                                                                                                                                                                          |                                                                                                                                                    |          |           |  |  |  |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|----------|-----------|--|--|--|
| <br><b>an INFINIT® brand</b><br>Website: <a href="http://www.L-com.com">www.L-com.com</a><br>Phone: 1.800.341.5266   1.978.682.6936 | <br>INTERPRET ALL DIMENSIONS AND<br>TOLERANCES PER ASME Y14.5 |          |           |  |  |  |
| SCALE                                                                                                                                                                                                                    |                                                                                                                                                    | SHEET    |           |  |  |  |
| NONE                                                                                                                                                                                                                     |                                                                                                                                                    | 2 OF 2   |           |  |  |  |
| DESCRIPTION                                                                                                                                                                                                              |                                                                                                                                                    |          |           |  |  |  |
| Cat6a FUTP RJ45 CMX LSZH 26AWG                                                                                                                                                                                           |                                                                                                                                                    |          |           |  |  |  |
| SIZE                                                                                                                                                                                                                     | CAGE CODE                                                                                                                                          | DRAWN BY | ITEM NO.  |  |  |  |
| A                                                                                                                                                                                                                        | 43321                                                                                                                                              | KGLEBOVA | TRD626ASZ |  |  |  |
|                                                                                                                                                                                                                          |                                                                                                                                                    |          | REV       |  |  |  |
|                                                                                                                                                                                                                          |                                                                                                                                                    |          | A         |  |  |  |

6

5

4

3

2

1