


8 7 6 5 4 3 2 1


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/2022	DGUITTADAURO

D C B A



**WIRING MAP**



**NOTES:**

- CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLYBAG PER L-COM SPECIFICATION PS-0031.
- CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
- PLUG ORIENTATION FOR REFERENCE ONLY.

**REGULATORY COMPLIANCE:**

EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm)		APPROVALS	DATE	 <b>an INFINITO brand</b> CATEGORY TELECOM/MODULAR	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
OVERALL CABLE LENGTH TOLERANCE:	≤12 (305) ≤+1 (25) / -0 ≤12 (305) ≤+2 (51) / -0 >60 (1524) ≤+4 (102) / -0 >120 (3048) ≤+6 (152) / -0 >300 (7620) ≤+5% / -0	DRAWN BY HBAKKE	12/15/2022		
ALL OTHER DIMENSIONAL TOLERANCES:	.X ± .2 (5) .XX ± .02 (15) .XXX ± .005 (13) FRACTIONS ± 1/32 ANGLES ± 1°	CHECKED BY DMAY	12/16/2022		
THIRD-ANGLE PROJECTION		APPROVED BY DGUST	12/16/2022	PRODUCT DESCRIPTION Category 6, Gigabit TAA Compliant Ethernet RJ45 to RJ45 Cable Assembly, 26AWG Stranded, UTP Unshielded, CM PVC	REV. A
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321
		SCALE: NONE	CAD FILE: TRD626TAA.SLDRW	ITEM NO. TRD626TAA	SHEET 1 OF 2

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER/COLOR/LENGTH TABLE

PART NUMBER	COLOR	LENGTH FEET [METERS]	LENGTH TOLERANCE FEET [METERS]
TRD626TAA-BLK-3F	BLACK	3.0 [0.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLK-5F	BLACK	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLK-7F	BLACK	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLK-10F	BLACK	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-15F	BLACK	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-25F	BLACK	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-50F	BLACK	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-75F	BLACK	75.0 [22.86]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-3F	BLUE	3.0 [0.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLU-5F	BLUE	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLU-7F	BLUE	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLU-10F	BLUE	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-15F	BLUE	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-25F	BLUE	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-50F	BLUE	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-75F	BLUE	75.0 [22.86]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-3F	GREEN	3.0 [0.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-GRN-5F	GREEN	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-GRN-7F	GREEN	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-GRN-10F	GREEN	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-15F	GREEN	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-25F	GREEN	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-50F	GREEN	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-75F	GREEN	75.0 [22.86]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-3F	YELLOW	3.0 [0.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-YLW-5F	YELLOW	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-YLW-7F	YELLOW	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-YLW-10F	YELLOW	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-15F	YELLOW	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-25F	YELLOW	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-50F	YELLOW	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-75F	YELLOW	75.0 [22.86]	+ .4/-0 [+ .12/-0]



50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

Category 6 Gigabit TAA Compliant Ethernet RJ45 to RJ45 Cable Assembly, 26AWG Stranded, UTP Unshielded, CM PVC

SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	TRD626TAA	A
SCALE: NONE	CAD FILE: TRD626TAA.SLDRW	SHEET 2 OF 2	