



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/2022	DGUITTADAURO



**WIRING MAP**



**NOTES:**

- CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLYBAG PER L-COM SPECIFICATION PS-0031.
- CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
- PLUG ORIENTATION FOR REFERENCE ONLY.

**REGULATORY COMPLIANCE:**

EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

 <b>an INFINITI brand</b>		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
APPROVALS	DATE	CATEGORY	
DRAWN BY HBAKKE	12/15/2022	TELECOM/MODULAR	
CHECKED BY DMAY	12/16/2022	PRODUCT DESCRIPTION	
APPROVED BY DGUST	12/16/2022	Category 6, Gigabit TAA Compliant Ethernet RJ45 to RJ45 Cable Assembly, 26AWG Stranded, UTP Unshielded, CM PVC	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm)		SIZE	ITEM NO.
OVERALL CABLE LENGTH TOLERANCE:		A	43321
$>12$ [305] $\leq 60$ [1524] = +1 [25] / -0 $>60$ [1524] $\leq 120$ [3048] = +2 [51] / -0 $>120$ [3048] $\leq 300$ [7620] = +4 [102] / -0 $>300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0		SCALE: NONE	CAD FILE: TRD626TAA.SLDRW
ALL OTHER DIMENSIONAL TOLERANCES:		REV.	
$.X = \pm .2$ [5] $.XX = \pm .02$ [1.5] $.XXX = \pm .005$ [1.3] FRACTIONS: $\pm 1/32$ ANGLES $\pm 1^\circ$		A	
THIRD-ANGLE PROJECTION		SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER/COLOR/LENGTH TABLE

PART NUMBER	COLOR	LENGTH FEET [METERS]	LENGTH TOLERANCE FEET [METERS]
TRD626TAA-BLK-3F	BLACK	3.0 [.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLK-5F	BLACK	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLK-7F	BLACK	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLK-10F	BLACK	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-15F	BLACK	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-25F	BLACK	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-50F	BLACK	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLK-75F	BLACK	75.0 [22.86]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-3F	BLUE	3.0 [.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLU-5F	BLUE	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLU-7F	BLUE	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-BLU-10F	BLUE	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-15F	BLUE	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-25F	BLUE	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-50F	BLUE	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-BLU-75F	BLUE	75.0 [22.86]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-3F	GREEN	3.0 [.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-GRN-5F	GREEN	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-GRN-7F	GREEN	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-GRN-10F	GREEN	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-15F	GREEN	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-25F	GREEN	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-50F	GREEN	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-GRN-75F	GREEN	75.0 [22.86]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-3F	YELLOW	3.0 [.91]	+ .2/-0 [+ .06/-0]
TRD626TAA-YLW-5F	YELLOW	5.0 [1.52]	+ .2/-0 [+ .06/-0]
TRD626TAA-YLW-7F	YELLOW	7.0 [2.13]	+ .2/-0 [+ .06/-0]
TRD626TAA-YLW-10F	YELLOW	10.0 [3.05]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-15F	YELLOW	15.0 [4.57]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-25F	YELLOW	25.0 [7.62]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-50F	YELLOW	50.0 [15.24]	+ .4/-0 [+ .12/-0]
TRD626TAA-YLW-75F	YELLOW	75.0 [22.86]	+ .4/-0 [+ .12/-0]



50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

Category: 6, Gigabit TAA, Compliant Ethernet RJ45 to RJ45 Cable Assembly, 26AWG, Stranded, UTP, Unshielded, CM PVC

SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	TRD626TAA	A
SCALE: NONE	CAD FILE: TRD626TAA.SLDRW	SHEET 2 OF 2	