

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION | | | | | |
|----------|-----|-----------------|-----------|------------|----------|
| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
| | A | INITIAL RELEASE | 6/28/2023 | DAVIDG | DAVIDG |

Overview
 Bandwidth: 500MHz
 OD:3.5mm
 Conductor: 28AWG
 Approvals: RoHS
 Connector: 50U" gold plated RJ45 connector

Physical Characteristics

- Cable Type: CAT6A UTP
- Connector Type(s): RJ45
- Wiring Scheme: T568B
- Temperature Rating
 - Installation: 0°C ~ 50°C
 - Operation: -20°C ~ 60°C
- Voltage Rating: 30V

Conductor (Qty, 4 twisted pair)

- Conductor Type: 28AWG(7/0.12±0.008mm), Stranded Bare Copper.
- Insulation: HDPE
- Diameter: 0.61±0.05mm
- Pair Identification:
 - Pair1 = Orange, Orange-White
 - Pair2 = Blue, Blue-White
 - Pair3 = Green, Green-White
 - Pair4 = Brown, Brown-White

Connector Type (Qty, 2)

- Connector Type: 8P8C (RJ45)
- Gender: Plug
- Connector Material: PC(94-V0)
- Contact Material: Copper Alloy, Gold Plating-50µm
- Hood Material: Transparent Assemble Boot

Overall Cable


- Jacket: CM PVC
- Minimum Average Thickness: 0.60mm
- Outer Diameter: 3.5±0.2mm

Electrical Characteristics


- Conductor DC Resistance: 28.4Ω/100m Max.
- Impedance: 100Ω
- Capacitance: 5600pf/100m
- Propagation Delay: 545ns/100m Max.
- Delay Skew: 45ns/100m Max.
- Pass Fluke DSX 8000 ISO Patch Cord Test (100%)



Miscellaneous

- Cable Assembly To Be Tested For Continuity
- Cable Assembly To Be Individually Packaged



WIRING MAP




| | | | | |
|---|--|--|---|------------------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13] | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | |
| | DRAWN BY KDANG | 6/1/2023 | | CATEGORY TELECOM/MODULAR |
| | CHECKED BY DAVIDG | 6/5/2023 | | |
| | APPROVED BY DAVIDG | 6/5/2023 | | |
| THIRD-ANGLE PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION Category 6A 10Gig Component Tested Slim Ethernet Cable Assembly | SIZE A | |
|  | COLOR VARIATIONS MAY OCCUR | CAGE CODE 43321 | ITEM NO. TRD695ACL | |
| | | SCALE: NONE | SHEET 1 OF 2 | |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| PART NUMBER | COLOR | LENGTH FEET [METERS] | TOLERANCE INCH [mm] |
|-------------------|-------|----------------------|-----------------------|
| TRD695ACL-BLK-05F | BLACK | 0.5 [0.15] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-BLK-1F | BLACK | 1.0 [0.30] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-BLK-3F | BLACK | 3.0 [0.91] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-BLK-5F | BLACK | 5.0 [1.52] | +1.38/-0.79 [+35/-20] |
| TRD695ACL-BLK-10F | BLACK | 10.0 [3.04] | +1.38/-1.18 [+35/-30] |
| TRD695ACL-BLK-15F | BLACK | 15.0 [4.57] | +1.38/-1.18 [+35/-30] |
| TRD695ACL-BLK-20F | BLACK | 20.0 [6.09] | ± 2.36[60] |
| TRD695ACL-BLK-25F | BLACK | 25.0 [7.62] | ± 2.36[60] |

| PART NUMBER | COLOR | LENGTH FEET [METERS] | TOLERANCE INCH [mm] |
|-------------------|-------|----------------------|-----------------------|
| TRD695ACL-BLU-05F | BLUE | 0.5 [0.15] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-BLU-1F | BLUE | 1.0 [0.30] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-BLU-3F | BLUE | 3.0 [0.91] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-BLU-5F | BLUE | 5.0 [1.52] | +1.38/-0.79 [+35/-20] |
| TRD695ACL-BLU-10F | BLUE | 10.0 [3.04] | +1.38/-1.18 [+35/-30] |
| TRD695ACL-BLU-15F | BLUE | 15.0 [4.57] | +1.38/-1.18 [+35/-30] |
| TRD695ACL-BLU-20F | BLUE | 20.0 [6.09] | ± 2.36[60] |
| TRD695ACL-BLU-25F | BLUE | 25.0 [7.62] | ± 2.36[60] |

| PART NUMBER | COLOR | LENGTH FEET [METERS] | TOLERANCE INCH [mm] |
|-------------------|-------|----------------------|-----------------------|
| TRD695ACL-GRY-05F | GRAY | 0.5 [0.15] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-GRY-1F | GRAY | 1.0 [0.30] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-GRY-3F | GRAY | 3.0 [0.91] | +1.38/-0.59 [+35/-15] |
| TRD695ACL-GRY-5F | GRAY | 5.0 [1.52] | +1.38/-0.79 [+35/-20] |
| TRD695ACL-GRY-10F | GRAY | 10.0 [3.04] | +1.38/-1.18 [+35/-30] |
| TRD695ACL-GRY-15F | GRAY | 15.0 [4.57] | +1.38/-1.18 [+35/-30] |
| TRD695ACL-GRY-20F | GRAY | 20.0 [6.09] | ± 2.36[60] |
| TRD695ACL-GRY-25F | GRAY | 25.0 [7.62] | ± 2.36[60] |

| | | | |
|--|---------------------------|---|------------------|
|  | | 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | |
| CATEGORY TELECOM/MODULAR | | | |
| PRODUCT DESCRIPTION Category 6A 10Gig Component Tested Slim Ethernet Cable Assembly | | | |
| SIZE A | CAGE CODE 43321 | ITEM NO. TRD695ACL | REV. A |
| SCALE: NONE | | CAD FILE: TRD695ACL.SLDDRW | |
| | | | SHEET 2 OF 2 |