




8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	01/17/2024	BZHANG	GUTTADAURO



- NOTES:**
1. PLUG CONFORMS TO TIA-1096.
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINIT® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY BZHANG		10/05/2023					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CHECKED BY GUTTADAURO		10/05/2023					
THIRD-ANGLE PROJECTION 		APPROVED BY GUTTADAURO		10/05/2023		CATEGORY		TELECOM/MODULAR	
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION C6A PVC F/UTP STR-UP					
		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. TRD695ASRA2	
				SCALE: NONE		CAD FILE: TRD695ASRA2.SLDDRW		REV. A	
								SHEET 1 OF 2	

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695ASRA2BLK-1	BLACK	1.0 [0.30]	TRD695ASRA2RED-1	RED	1.0 [0.30]	TRD695ASRA2GRY-1	GRAY	1.0 [0.30]	TRD695ASRA2YEL-1	YELLOW	1.0 [0.30]
TRD695ASRA2BLK-2	BLACK	2.0 [0.61]	TRD695ASRA2RED-2	RED	2.0 [0.61]	TRD695ASRA2GRY-2	GRAY	2.0 [0.61]	TRD695ASRA2YEL-2	YELLOW	2.0 [0.61]
TRD695ASRA2BLK-3	BLACK	3.0 [0.91]	TRD695ASRA2RED-3	RED	3.0 [0.91]	TRD695ASRA2GRY-3	GRAY	3.0 [0.91]	TRD695ASRA2YEL-3	YELLOW	3.0 [0.91]
TRD695ASRA2BLK-5	BLACK	5.0 [1.52]	TRD695ASRA2RED-5	RED	5.0 [1.52]	TRD695ASRA2GRY-5	GRAY	5.0 [1.52]	TRD695ASRA2YEL-5	YELLOW	5.0 [1.52]
TRD695ASRA2BLK-7	BLACK	7.0 [2.13]	TRD695ASRA2RED-7	RED	7.0 [2.13]	TRD695ASRA2GRY-7	GRAY	7.0 [2.13]	TRD695ASRA2YEL-7	YELLOW	7.0 [2.13]
TRD695ASRA2BLK-10	BLACK	10.0 [3.05]	TRD695ASRA2RED-10	RED	10.0 [3.05]	TRD695ASRA2GRY-10	GRAY	10.0 [3.05]	TRD695ASRA2YEL-10	YELLOW	10.0 [3.05]
TRD695ASRA2BLK-15	BLACK	15.0 [4.57]	TRD695ASRA2RED-15	RED	15.0 [4.57]	TRD695ASRA2GRY-15	GRAY	15.0 [4.57]	TRD695ASRA2YEL-15	YELLOW	15.0 [4.57]
TRD695ASRA2BLK-20	BLACK	20.0 [6.10]	TRD695ASRA2RED-20	RED	20.0 [6.10]	TRD695ASRA2GRY-20	GRAY	20.0 [6.10]	TRD695ASRA2YEL-20	YELLOW	20.0 [6.10]
TRD695ASRA2BLU-1	BLUE	1.0 [0.30]	TRD695ASRA2GRN-1	GREEN	1.0 [0.30]	TRD695ASRA2ORG-1	ORANGE	1.0 [0.30]			
TRD695ASRA2BLU-2	BLUE	2.0 [0.61]	TRD695ASRA2GRN-2	GREEN	2.0 [0.61]	TRD695ASRA2ORG-2	ORANGE	2.0 [0.61]			
TRD695SARA2BLU-3	BLUE	3.0 [0.91]	TRD695ASRA2GRN-3	GREEN	3.0 [0.91]	TRD695ASRA2ORG-3	ORANGE	3.0 [0.91]			
TRD695ASRA2BLU-5	BLUE	5.0 [1.52]	TRD695ASRA2GRN-5	GREEN	5.0 [1.52]	TRD695ASRA2ORG-5	ORANGE	5.0 [1.52]			
TRD695ASRA2BLU-7	BLUE	7.0 [2.13]	TRD695ASRA2GRN-7	GREEN	7.0 [2.13]	TRD695ASRA2ORG-7	ORANGE	7.0 [2.13]			
TRD695ASRA2BLU-10	BLUE	10.0 [3.05]	TRD695ASRA2GRN-10	GREEN	10.0 [3.05]	TRD695ASRA2ORG-10	ORANGE	10.0 [3.05]			
TRD695ASRA2BLU-15	BLUE	15.0 [4.57]	TRD695ASRA2GRN-15	GREEN	15.0 [4.57]	TRD695ASRA2ORG-15	ORANGE	15.0 [4.57]			
TRD695ASRA2BLU-20	BLUE	20.0 [6.10]	TRD695ASRA2GRN-20	GREEN	20.0 [6.10]	TRD695ASRA2ORG-20	ORANGE	20.0 [6.10]			



an INFINITE brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

C6A PVC F/UTP STR-UP

SIZE
A

CAGE CODE
43321

ITEM NO.
TRD695ASRA2

REV.
A

SCALE: NONE

CAD FILE: TRD695ASRA2.SLDDRW

SHEET 2 OF 2