


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	01/17/2024	BZHANG	GUTTADAURO



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13] FRACTIONS ± 1/32 ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY BZHANG	10/05/2023	
	CHECKED BY GUTTADAURO	10/05/2023	
	APPROVED BY GUTTADAURO	10/05/2023	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY TELECOM/MODULAR		PRODUCT DESCRIPTION C6A PVC F/UTP STR-RGT
	COLOR VARIATIONS MAY OCCUR	SIZE A	
	CAGE CODE 43321	ITEM NO. TRD695ASRA7	
SCALE: NONE		CAD FILE: TRD695ASRA7.SLDDRW	REV. A
		SHEET 1 OF 2	

8			7			6			5			4			3			2			1		
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.																							
PART NUMBER			COLOR	LENGTH FEET [METERS]		PART NUMBER			COLOR	LENGTH FEET [METERS]		PART NUMBER			COLOR	LENGTH FEET [METERS]		PART NUMBER			COLOR	LENGTH FEET [METERS]	
TRD695ASRA7BLK-1			BLACK	1.0 [0.30]		TRD695ASRA7RED-1			RED	1.0 [0.30]		TRD695ASRA7GRY-1			GRAY	1.0 [0.30]		TRD695ASRA7YEL-1			YELLOW	1.0 [0.30]	
TRD695ASRA7BLK-2			BLACK	2.0 [0.61]		TRD695ASRA7RED-2			RED	2.0 [0.61]		TRD695ASRA7GRY-2			GRAY	2.0 [0.61]		TRD695ASRA7YEL-2			YELLOW	2.0 [0.61]	
TRD695ASRA7BLK-3			BLACK	3.0 [0.91]		TRD695ASRA7RED-3			RED	3.0 [0.91]		TRD695ASRA7GRY-3			GRAY	3.0 [0.91]		TRD695ASRA7YEL-3			YELLOW	3.0 [0.91]	
TRD695ASRA7BLK-5			BLACK	5.0 [1.52]		TRD695ASRA7RED-5			RED	5.0 [1.52]		TRD695ASRA7GRY-5			GRAY	5.0 [1.52]		TRD695ASRA7YEL-5			YELLOW	5.0 [1.52]	
TRD695ASRA7BLK-7			BLACK	7.0 [2.13]		TRD695ASRA7RED-7			RED	7.0 [2.13]		TRD695ASRA7GRY-7			GRAY	7.0 [2.13]		TRD695ASRA7YEL-7			YELLOW	7.0 [2.13]	
TRD695ASRA7BLK-10			BLACK	10.0 [3.05]		TRD695ASRA7RED-10			RED	10.0 [3.05]		TRD695ASRA7GRY-10			GRAY	10.0 [3.05]		TRD695ASRA7YEL-10			YELLOW	10.0 [3.05]	
TRD695ASRA7BLK-15			BLACK	15.0 [4.57]		TRD695ASRA7RED-15			RED	15.0 [4.57]		TRD695ASRA7GRY-15			GRAY	15.0 [4.57]		TRD695ASRA7YEL-15			YELLOW	15.0 [4.57]	
TRD695ASRA7BLK-20			BLACK	20.0 [6.10]		TRD695ASRA7RED-20			RED	20.0 [6.10]		TRD695ASRA7GRY-20			GRAY	20.0 [6.10]		TRD695ASRA7YEL-20			YELLOW	20.0 [6.10]	
TRD695ASRA7BLU-1			BLUE	1.0 [0.30]		TRD695ASRA7GRN-1			GREEN	1.0 [0.30]		TRD695ASRA7ORG-1			ORANGE	1.0 [0.30]							
TRD695ASRA7BLU-2			BLUE	2.0 [0.61]		TRD695ASRA7GRN-2			GREEN	2.0 [0.61]		TRD695ASRA7ORG-2			ORANGE	2.0 [0.61]							
TRD695SARA7BLU-3			BLUE	3.0 [0.91]		TRD695ASRA7GRN-3			GREEN	3.0 [0.91]		TRD695ASRA7ORG-3			ORANGE	3.0 [0.91]							
TRD695ASRA7BLU-5			BLUE	5.0 [1.52]		TRD695ASRA7GRN-5			GREEN	5.0 [1.52]		TRD695ASRA7ORG-5			ORANGE	5.0 [1.52]							
TRD695ASRA7BLU-7			BLUE	7.0 [2.13]		TRD695ASRA7GRN-7			GREEN	7.0 [2.13]		TRD695ASRA7ORG-7			ORANGE	7.0 [2.13]							
TRD695ASRA7BLU-10			BLUE	10.0 [3.05]		TRD695ASRA7GRN-10			GREEN	10.0 [3.05]		TRD695ASRA7ORG-10			ORANGE	10.0 [3.05]							
TRD695ASRA7BLU-15			BLUE	15.0 [4.57]		TRD695ASRA7GRN-15			GREEN	15.0 [4.57]		TRD695ASRA7ORG-15			ORANGE	15.0 [4.57]							
TRD695ASRA7BLU-20			BLUE	20.0 [6.10]		TRD695ASRA7GRN-20			GREEN	20.0 [6.10]		TRD695ASRA7ORG-20			ORANGE	20.0 [6.10]							