



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	01/17/2024	BZHANG	GUTTADAURO




P1
SHIELDED RJ45 MODULAR PLUG
GOLD PLATED CONTACTS
(8P8C)

P2
SHIELDED RJ45 MODULAR PLUG
GOLD PLATED CONTACTS
(8P8C)

RIGHT ANGLE MOLDED BOOT
WITH BOTH SIDES LOGO
PVC, COLOR: BLACK
SHIELD: COPPER FOIL

CAT 6a F/UTP SHIELD CABLE
4 TWISTED PAIR, 26AWG STRANDED COPPER CONDUCTORS
WITH ALUMINIZED POLYESTER SHIELD AND STRANDED
TINNED COPPER DRAIN WIRE
JACKET: CMX PVC, COLOR: SEE SHEET 2
(TEMPERATURE RANGE: -20 °C TO +75 °C; NOM. DIA: .236 [6.0])



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13] FRACTIONS ± 1/32 ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY BZHANG	10/05/2023	
	CHECKED BY GUTTADAURO	10/05/2023	
	APPROVED BY GUTTADAURO	10/05/2023	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY TELECOM/MODULAR		PRODUCT DESCRIPTION C6A PVC F/UTP STR-RGT
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	
	ITEM NO. TRD695ASRA7	REV. A	
	SCALE: NONE	CAD FILE: TRD695ASRA7.SLDDRW	

8			7			6			5			4			3			2			1					
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.																										
PART NUMBER			COLOR			LENGTH FEET [METERS]			PART NUMBER			COLOR			LENGTH FEET [METERS]			PART NUMBER			COLOR			LENGTH FEET [METERS]		
TRD695ASRA7BLK-1			BLACK			1.0 [0.30]			TRD695ASRA7RED-1			RED			1.0 [0.30]			TRD695ASRA7GRY-1			GRAY			1.0 [0.30]		
TRD695ASRA7BLK-2			BLACK			2.0 [0.61]			TRD695ASRA7RED-2			RED			2.0 [0.61]			TRD695ASRA7GRY-2			GRAY			2.0 [0.61]		
TRD695ASRA7BLK-3			BLACK			3.0 [0.91]			TRD695ASRA7RED-3			RED			3.0 [0.91]			TRD695ASRA7GRY-3			GRAY			3.0 [0.91]		
TRD695ASRA7BLK-5			BLACK			5.0 [1.52]			TRD695ASRA7RED-5			RED			5.0 [1.52]			TRD695ASRA7GRY-5			GRAY			5.0 [1.52]		
TRD695ASRA7BLK-7			BLACK			7.0 [2.13]			TRD695ASRA7RED-7			RED			7.0 [2.13]			TRD695ASRA7GRY-7			GRAY			7.0 [2.13]		
TRD695ASRA7BLK-10			BLACK			10.0 [3.05]			TRD695ASRA7RED-10			RED			10.0 [3.05]			TRD695ASRA7GRY-10			GRAY			10.0 [3.05]		
TRD695ASRA7BLK-15			BLACK			15.0 [4.57]			TRD695ASRA7RED-15			RED			15.0 [4.57]			TRD695ASRA7GRY-15			GRAY			15.0 [4.57]		
TRD695ASRA7BLK-20			BLACK			20.0 [6.10]			TRD695ASRA7RED-20			RED			20.0 [6.10]			TRD695ASRA7GRY-20			GRAY			20.0 [6.10]		
TRD695ASRA7BLU-1			BLUE			1.0 [0.30]			TRD695ASRA7GRN-1			GREEN			1.0 [0.30]			TRD695ASRA7ORG-1			ORANGE			1.0 [0.30]		
TRD695ASRA7BLU-2			BLUE			2.0 [0.61]			TRD695ASRA7GRN-2			GREEN			2.0 [0.61]			TRD695ASRA7ORG-2			ORANGE			2.0 [0.61]		
TRD695SARA7BLU-3			BLUE			3.0 [0.91]			TRD695ASRA7GRN-3			GREEN			3.0 [0.91]			TRD695ASRA7ORG-3			ORANGE			3.0 [0.91]		
TRD695ASRA7BLU-5			BLUE			5.0 [1.52]			TRD695ASRA7GRN-5			GREEN			5.0 [1.52]			TRD695ASRA7ORG-5			ORANGE			5.0 [1.52]		
TRD695ASRA7BLU-7			BLUE			7.0 [2.13]			TRD695ASRA7GRN-7			GREEN			7.0 [2.13]			TRD695ASRA7ORG-7			ORANGE			7.0 [2.13]		
TRD695ASRA7BLU-10			BLUE			10.0 [3.05]			TRD695ASRA7GRN-10			GREEN			10.0 [3.05]			TRD695ASRA7ORG-10			ORANGE			10.0 [3.05]		
TRD695ASRA7BLU-15			BLUE			15.0 [4.57]			TRD695ASRA7GRN-15			GREEN			15.0 [4.57]			TRD695ASRA7ORG-15			ORANGE			15.0 [4.57]		
TRD695ASRA7BLU-20			BLUE			20.0 [6.10]			TRD695ASRA7GRN-20			GREEN			20.0 [6.10]			TRD695ASRA7ORG-20			ORANGE			20.0 [6.10]		