



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/17/17	D.FRISIELLO



- NOTES:**
- LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


**CABLE CHARACTERISTICS:**  
 FLAME RATING: VW-1, UL TYPE CMX  
 CORROSIVE GAS: IEC 60754  
 SMOKE EMISSION: IEC 61034

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845		
	DRAWN BY D.FRISIELLO	8/14/17				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY M.MARTINEZ	8/17/17		<b>TELECOM/MODULAR</b>		
	APPROVED BY D.GUITADAURO	8/17/17		CATEGORY <b>TELECOM/MODULAR</b>		
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>RJ45 C6a F/UTP LSZH</b>	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>TRD695ASZ</b>	REV. <b>A</b>
	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: TRD695ASZ.SLDDRW	SHEET 1 OF 2		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NUMBER	COLOR	LENGTH		MODEL NUMBER	COLOR	LENGTH		MODEL NUMBER	COLOR	LENGTH	
		FEET	METERS			FEET	METERS			FEET	METERS
TRD695ASZRED-1	RED	1.0	0.30	TRD695ASZBLU-1	BLUE	1.0	0.30	TRD695ASZBLK-1	BLACK	1.0	0.30
TRD695ASZRED-2	RED	2.0	0.61	TRD695ASZBLU-2	BLUE	2.0	0.61	TRD695ASZBLK-2	BLACK	2.0	0.61
TRD695ASZRED-3	RED	3.0	0.91	TRD695ASZBLU-3	BLUE	3.0	0.91	TRD695ASZBLK-3	BLACK	3.0	0.91
TRD695ASZRED-5	RED	5.0	1.52	TRD695ASZBLU-5	BLUE	5.0	1.52	TRD695ASZBLK-5	BLACK	5.0	1.52
TRD695ASZRED-7	RED	7.0	2.13	TRD695ASZBLU-7	BLUE	7.0	2.13	TRD695ASZBLK-7	BLACK	7.0	2.13
TRD695ASZRED-10	RED	10.0	3.05	TRD695ASZBLU-10	BLUE	10.0	3.05	TRD695ASZBLK-10	BLACK	10.0	3.05
TRD695ASZRED-15	RED	15.0	4.57	TRD695ASZBLU-15	BLUE	15.0	4.57	TRD695ASZBLK-15	BLACK	15.0	4.57
TRD695ASZRED-20	RED	20.0	6.10	TRD695ASZBLU-20	BLUE	20.0	6.10	TRD695ASZBLK-20	BLACK	20.0	6.10
TRD695ASZRED-25	RED	25.0	7.62	TRD695ASZBLU-25	BLUE	25.0	7.62	TRD695ASZBLK-25	BLACK	25.0	7.62
TRD695ASZRED-30	RED	30.0	9.14	TRD695ASZBLU-30	BLUE	30.0	9.14	TRD695ASZBLK-30	BLACK	30.0	9.14
TRD695ASZRED-50	RED	50.0	15.24	TRD695ASZBLU-50	BLUE	50.0	15.24	TRD695ASZBLK-50	BLACK	50.0	15.24
TRD695ASZRED-75	RED	75.0	22.86	TRD695ASZBLU-75	BLUE	75.0	22.86	TRD695ASZBLK-75	BLACK	75.0	22.86
TRD695ASZRED-100	RED	100.0	30.48	TRD695ASZBLU-100	BLUE	100.0	30.48	TRD695ASZBLK-100	BLACK	100.0	30.48

		50 HIGH STREET NORTH ANDOVER, MA 01845	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
RJ45 C6a F/UTP LSZH			
SIZE	FSCM NO.	DWG. NO.	REV.
<b>A</b>	<b>43321</b>	TRD695ASZ	<b>A</b>
SCALE: NONE		CAD FILE: TRD695ASZ.SLDDRW	SHEET 2 OF 2