



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/12/11	D.GRIFFIN
B	ECN 7015: REVISED L-COM LOGO, ROHS, FORMAT, ADDED CHANNEL NOTE	8/13/13	D.FRISIELLO
C	ECN 7274: REMOVED DRAIN WIRE FROM DESCRIPTION	1/31/14	D.FRISIELLO



NOTES:

MATERIAL:

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 CONTACTS: PHOSPHOR BRONZE
 CABLE JACKET: LOW SMOKE, ZERO HALOGEN, COLOR: SEE CHART
 PLUG SHIELDING: BRASS
 SNAGLESS BOOT: LOW SMOKE, ZERO HALOGEN, BLACK

FINISH:

CONTACTS: 50 μINCHES GOLD PLATED IN CONTACT AREA
 OVER 100 μINCHES NICKEL PLATE OVERALL
 PLUG SHIELDING: NICKEL PLATED

CABLE CHARACTERISTICS:

SHIELDED, FOUR TWISTED PAIR, CAT 6 MODULAR CABLE
 CONDUCTORS: 26 AWG STRANDED BARE COPPER WITH ALUMINUM/ POLYESTER FOIL SHIELD AND TINNED COPPER BRAID SHIELD.


MISCELLANEOUS:

LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
 PLUG CONFORMS TO TIA-1096.
 CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

WIRING MAP



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY J.RUST APPROVED BY D.GALLAGHER	DATE 4/26/11 4/26/11 4/26/11	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845				
	CATEGORY TELECOM/MODULAR			PRODUCT DESCRIPTION CATEGORY 6 DBL SHIELDED LSZH PATCH CORD			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. TRD695DSZ
	SCALE: NONE		CAD FILE: TRD695DSZ.SLDDRW		SHEET 1 OF 2		

