



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/30/14	D.GRIFFIN



MODEL NUMBER	LENGTH FEET [METERS]	MODEL NUMBER	LENGTH FEET [METERS]
TRD695SPL-1	1.0 [.30]	TRD695SPL-25	25.0 [7.62]
TRD695SPL-2	2.0 [.61]	TRD695SPL-30	30.0 [9.14]
TRD695SPL-3	3.0 [.91]	TRD695SPL-40	40.0 [12.19]
TRD695SPL-5	5.0 [1.52]	TRD695SPL-50	50.0 [15.24]
TRD695SPL-7	7.0 [2.13]	TRD695SPL-60	60.0 [18.29]
TRD695SPL-10	10.0 [3.05]	TRD695SPL-75	75.0 [22.86]
TRD695SPL-15	15.0 [4.57]	TRD695SPL-100	100.0 [30.48]
TRD695SPL-20	20.0 [6.10]		

- NOTES:**
- LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
  - PLUG CONFORMS TO TIA-1096.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	10/29/14		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D.GUITADAURO	10/29/14	CATEGORY <b>TELECOM/MODULAR</b>	
	APPROVED BY M.MARTINEZ	10/30/14	PRODUCT DESCRIPTION <b>RJ45 C6 FUTP 23SLD CMP WHT</b>	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. <b>TRD695SPL</b>	REV. <b>A</b>
			SCALE: NONE	CAD FILE: TRD695SPL.SLDDRW
				SHEET 1 OF 1