



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/13/12	D.GRIFFIN
B	ECN6442: ADDED CHANNEL RATING NOTE	1/22/13	D. DESJARDIN
C	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/13/14	D.FRISIELLO



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	APPROVALS D. DESJARDIN CHECKED BY J. RUST APPROVED BY D. GALLAGHER	DATE 3/6/12 3/8/12 3/8/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. TRD695SRA9		SCALE: NONE	CAD FILE: TRD695SRA9.SLDDRW
			REV. C	
			SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695SRA9BLK-1	BLACK	1.0 [0.30]	TRD695SRA9RD-1	RED	1.0 [0.30]	TRD695SRA9GRY-1	GRAY	1.0 [0.30]	TRD695SRA9Y-1	YELLOW	1.0 [0.30]
TRD695SRA9BLK-2	BLACK	2.0 [0.61]	TRD695SRA9RD-2	RED	2.0 [0.61]	TRD695SRA9GRY-2	GRAY	2.0 [0.61]	TRD695SRA9Y-2	YELLOW	2.0 [0.61]
TRD695SRA9BLK-3	BLACK	3.0 [0.91]	TRD695SRA9RD-3	RED	3.0 [0.91]	TRD695SRA9GRY-3	GRAY	3.0 [0.91]	TRD695SRA9Y-3	YELLOW	3.0 [0.91]
TRD695SRA9BLK-5	BLACK	5.0 [1.52]	TRD695SRA9RD-5	RED	5.0 [1.52]	TRD695SRA9GRY-5	GRAY	5.0 [1.52]	TRD695SRA9Y-5	YELLOW	5.0 [1.52]
TRD695SRA9BLK-7	BLACK	7.0 [2.13]	TRD695SRA9RD-7	RED	7.0 [2.13]	TRD695SRA9GRY-7	GRAY	7.0 [2.13]	TRD695SRA9Y-7	YELLOW	7.0 [2.13]
TRD695SRA9BLK-10	BLACK	10.0 [3.05]	TRD695SRA9RD-10	RED	10.0 [3.05]	TRD695SRA9GRY-10	GRAY	10.0 [3.05]	TRD695SRA9Y-10	YELLOW	10.0 [3.05]
TRD695SRA9BLK-15	BLACK	15.0 [4.57]	TRD695SRA9RD-15	RED	15.0 [4.57]	TRD695SRA9GRY-15	GRAY	15.0 [4.57]	TRD695SRA9Y-15	YELLOW	15.0 [4.57]
TRD695SRA9BLK-20	BLACK	20.0 [6.10]	TRD695SRA9RD-20	RED	20.0 [6.10]	TRD695SRA9GRY-20	GRAY	20.0 [6.10]	TRD695SRA9Y-20	YELLOW	20.0 [6.10]
TRD695SRA9BLK-25	BLACK	25.0 [7.62]	TRD695SRA9RD-25	RED	25.0 [7.62]	TRD695SRA9GRY-25	GRAY	25.0 [7.62]	TRD695SRA9Y-25	YELLOW	25.0 [7.62]
TRD695SRA9BLK-30	BLACK	30.0 [9.14]	TRD695SRA9RD-30	RED	30.0 [9.14]	TRD695SRA9GRY-30	GRAY	30.0 [9.14]	TRD695SRA9Y-30	YELLOW	30.0 [9.14]
TRD695SRA9BL-1	BLUE	1.0 [0.30]	TRD695SRA9GR-1	GREEN	1.0 [0.30]	TRD695SRA9OR-1	ORANGE	1.0 [0.30]			
TRD695SRA9BL-2	BLUE	2.0 [0.61]	TRD695SRA9GR-2	GREEN	2.0 [0.61]	TRD695SRA9OR-2	ORANGE	2.0 [0.61]			
TRD695SRA9BL-3	BLUE	3.0 [0.91]	TRD695SRA9GR-3	GREEN	3.0 [0.91]	TRD695SRA9OR-3	ORANGE	3.0 [0.91]			
TRD695SRA9BL-5	BLUE	5.0 [1.52]	TRD695SRA9GR-5	GREEN	5.0 [1.52]	TRD695SRA9OR-5	ORANGE	5.0 [1.52]			
TRD695SRA9BL-7	BLUE	7.0 [2.13]	TRD695SRA9GR-7	GREEN	7.0 [2.13]	TRD695SRA9OR-7	ORANGE	7.0 [2.13]			
TRD695SRA9BL-10	BLUE	10.0 [3.05]	TRD695SRA9GR-10	GREEN	10.0 [3.05]	TRD695SRA9OR-10	ORANGE	10.0 [3.05]			
TRD695SRA9BL-15	BLUE	15.0 [4.57]	TRD695SRA9GR-15	GREEN	15.0 [4.57]	TRD695SRA9OR-15	ORANGE	15.0 [4.57]			
TRD695SRA9BL-20	BLUE	20.0 [6.10]	TRD695SRA9GR-20	GREEN	20.0 [6.10]	TRD695SRA9OR-20	ORANGE	20.0 [6.10]			
TRD695SRA9BL-25	BLUE	25.0 [7.62]	TRD695SRA9GR-25	GREEN	25.0 [7.62]	TRD695SRA9OR-25	ORANGE	25.0 [7.62]			
TRD695SRA9BL-30	BLUE	30.0 [9.14]	TRD695SRA9GR-30	GREEN	30.0 [9.14]	TRD695SRA9OR-30	ORANGE	30.0 [9.14]			

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C6 PVC FTP LFT-LFT			
SIZE A	FSCM NO. 43321	DWG. NO. TRD695SRA9	REV. C
SCALE: NONE		CAD FILE: TRD695SRA9.SLDDRW	
			SHEET 2 OF 2