



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
L	ECN 9218: REMOVE "SHIELDED" FROM TWISTED PAIR, NEW FORMAT	5/29/18	D.FRISIELLO




2X, LOGO BOTH SIDES



"P1"

"P2"




POSITION 1

POSITION 1

2X, SHIELDED RJ45 MODULAR PLUG
GOLD PLATED CONTACTS
(8P8C)

2X, SNAGLESS SLIP-ON BOOT
LSZH, BLACK

FOUR TWISTED PAIRS, CATEGORY 6
26 AWG STRANDED COPPER WITH
ALUMINUM/POLYESTER SHIELDING AND DRAIN WIRE
LOW SMOKE ZERO HALOGEN JACKET
SEE SHEET 2 FOR COLOR



NOTES:


1. LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
2. PLUG CONFORMS TO TIA-1096.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [51] .XXX = $\pm .005$ [1.27]	APPROVALS DRAWN BY D. PARHAM CHECKED BY J. KIEZULAS APPROVED BY C. McCORMICK	DATE 03/15/2006 03/16/2006 03/16/2006	L-com Global Connectivity 50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR	
PROJECTION 	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION CBL RJ45 CAT 6 SHLD LSZH	
SCALE: NONE		SIZE A	FSCM NO. 43321	DWG. NO. TRD695SZ
CAD FILE: TRD695SZ.SLDDRW			SHEET 1 OF 2	REV. L

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695SZ-1	LIGHT GRAY	1.0 [0.30]	TRD695SZBLK-1	BLACK	1.0 [0.30]	TRD695SZR-1	RED	1.0 [0.30]
TRD695SZ-2	LIGHT GRAY	2.0 [0.61]	TRD695SZBLK-2	BLACK	2.0 [0.61]	TRD695SZR-2	RED	2.0 [0.61]
TRD695SZ-3	LIGHT GRAY	3.0 [0.91]	TRD695SZBLK-3	BLACK	3.0 [0.91]	TRD695SZR-3	RED	3.0 [0.91]
TRD695SZ-5	LIGHT GRAY	5.0 [1.52]	TRD695SZBLK-5	BLACK	5.0 [1.52]	TRD695SZR-5	RED	5.0 [1.52]
TRD695SZ-7	LIGHT GRAY	7.0 [2.13]	TRD695SZBLK-7	BLACK	7.0 [2.13]	TRD695SZR-7	RED	7.0 [2.13]
TRD695SZ-10	LIGHT GRAY	10.0 [3.05]	TRD695SZBLK-10	BLACK	10.0 [3.05]	TRD695SZR-10	RED	10.0 [3.05]
TRD695SZ-15	LIGHT GRAY	15.0 [4.57]	TRD695SZBLK-15	BLACK	15.0 [4.57]	TRD695SZR-15	RED	15.0 [4.57]
TRD695SZ-20	LIGHT GRAY	20.0 [6.10]	TRD695SZBLK-20	BLACK	20.0 [6.10]	TRD695SZR-20	RED	20.0 [6.10]
TRD695SZ-25	LIGHT GRAY	25.0 [7.62]	TRD695SZBLK-25	BLACK	25.0 [7.62]	TRD695SZR-25	RED	25.0 [7.62]
TRD695SZ-30	LIGHT GRAY	30.0 [9.14]	TRD695SZBLK-30	BLACK	30.0 [9.14]	TRD695SZR-30	RED	30.0 [9.14]
TRD695SZ-40	LIGHT GRAY	40.0 [12.19]	TRD695SZBLK-40	BLACK	40.0 [12.19]	TRD695SZR-40	RED	40.0 [12.19]
TRD695SZ-50	LIGHT GRAY	50.0 [15.24]	TRD695SZBLK-50	BLACK	50.0 [15.24]	TRD695SZR-50	RED	50.0 [15.24]
TRD695SZ-60	LIGHT GRAY	60.0 [18.29]	TRD695SZBLK-60	BLACK	60.0 [18.29]	TRD695SZR-60	RED	60.0 [18.29]
TRD695SZ-75	LIGHT GRAY	75.0 [22.86]	TRD695SZBLK-75	BLACK	75.0 [22.86]	TRD695SZR-75	RED	75.0 [22.86]
TRD695SZ-80	LIGHT GRAY	80.0 [24.38]	TRD695SZBLK-100	BLACK	100.0 [30.48]	TRD695SZR-100	RED	100.0 [30.48]
TRD695SZ-90	LIGHT GRAY	90.0 [27.43]						
TRD695SZ-100	LIGHT GRAY	100.0 [30.48]						
TRD695SZ-150	LIGHT GRAY	150.0 [45.72]						
TRD695SZ-200	LIGHT GRAY	200.0 [60.96]						
TRD695SZ-250	LIGHT GRAY	250.0 [76.20]						
TRD695SZ-300	LIGHT GRAY	300.0 [91.44]						

		50 HIGH STREET NORTH ANDOVER, MA 01845	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
CBL RJ45 CAT 6 SHLD LSZH			
SIZE	FSCM NO.	DWG. NO.	REV.
A	43321	TRD695SZ	L
SCALE: NONE		CAD FILE: TRD695SZ.SLDDRW	
			SHEET 2 OF 2