



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/21/12	D.GRIFFIN
B	ECN 6202: CHANGED BOOTS TO "PE"	6/4/12	D. DESJARDIN
C	ECN6548: UPDATED NOTES. CHANGED PE NOTE TO LSZH	12/3/12	D. DESJARDIN
D	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/26/14	D.FRISIELLO



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $>12 [305] \leq 60 [1524] = +2 [51] / -0$ $>60 [1524] \leq 120 [3048] = +4 [102] / -0$ $>120 [3048] \leq 300 [7620] = +6 [152] / -0$ $>300 [7620] = +5\% / -0\%$ ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2 [5.08]$.XX = $\pm .02 [.51]$.XXX = $\pm .005 [.13]$	APPROVALS DRAWN BY D. DESJARDIN CHECKED BY J. RUST APPROVED BY D. GALLAGHER	DATE 3/14/12 3/16/12 3/20/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. TRD695SZRA11		REV. D	SCALE: NONE CAD FILE: TRD695SZRA11.SLDDRW SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695SZRA11BLK-1	BLACK	1.0 [0.30]	TRD695SZRA11RD-1	RED	1.0 [0.30]	TRD695SZRA11GRY-1	GRAY	1.0 [0.30]
TRD695SZRA11BLK-2	BLACK	2.0 [0.61]	TRD695SZRA11RD-2	RED	2.0 [0.61]	TRD695SZRA11GRY-2	GRAY	2.0 [0.61]
TRD695SZRA11BLK-3	BLACK	3.0 [0.91]	TRD695SZRA11RD-3	RED	3.0 [0.91]	TRD695SZRA11GRY-3	GRAY	3.0 [0.91]
TRD695SZRA11BLK-5	BLACK	5.0 [1.52]	TRD695SZRA11RD-5	RED	5.0 [1.52]	TRD695SZRA11GRY-5	GRAY	5.0 [1.52]
TRD695SZRA11BLK-7	BLACK	7.0 [2.13]	TRD695SZRA11RD-7	RED	7.0 [2.13]	TRD695SZRA11GRY-7	GRAY	7.0 [2.13]
TRD695SZRA11BLK-10	BLACK	10.0 [3.05]	TRD695SZRA11RD-10	RED	10.0 [3.05]	TRD695SZRA11GRY-10	GRAY	10.0 [3.05]
TRD695SZRA11BLK-15	BLACK	15.0 [4.57]	TRD695SZRA11RD-15	RED	15.0 [4.57]	TRD695SZRA11GRY-15	GRAY	15.0 [4.57]
TRD695SZRA11BLK-20	BLACK	20.0 [6.10]	TRD695SZRA11RD-20	RED	20.0 [6.10]	TRD695SZRA11GRY-20	GRAY	20.0 [6.10]
TRD695SZRA11BLK-25	BLACK	25.0 [7.62]	TRD695SZRA11RD-25	RED	25.0 [7.62]	TRD695SZRA11GRY-25	GRAY	25.0 [7.62]
TRD695SZRA11BLK-30	BLACK	30.0 [9.14]	TRD695SZRA11RD-30	RED	30.0 [9.14]	TRD695SZRA11GRY-30	GRAY	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C6 LSZ FTP LFT-DWN			
SIZE A	FSCM NO. 43321	DWG. NO. TRD695SZRA11	REV. D
SCALE: NONE		CAD FILE: TRD695SZRA11.SLDDRW	SHEET 2 OF 2