



8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/21/12	D.GRIFFIN
B	ECN 6202: CHANGED BOOTS TO "PE"	6/5/12	D. DESJARDIN
C	ECN6548: UPDATED NOTES. CHANGED PE NOTE TO LSZH	12/4/12	D. DESJARDIN
D	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/26/14	D.FRISIELLO



**NOTES:**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	3/14/12		CATEGORY <b>TELECOM/MODULAR</b>
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY J. RUST	3/16/12	PRODUCT DESCRIPTION <b>C6 LSZ FTP RGT-RGT</b>	
PROJECTION 	APPROVED BY D. GALLAGHER	3/20/12	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. <b>TRD695SZRA14</b>	REV. <b>D</b>
			CAD FILE: TRD695SZRA14.SLDDRW	SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695SZRA14BLK-1	BLACK	1.0 [0.30]	TRD695SZRA14RD-1	RED	1.0 [0.30]	TRD695SZRA14GRY-1	GRAY	1.0 [0.30]
TRD695SZRA14BLK-2	BLACK	2.0 [0.61]	TRD695SZRA14RD-2	RED	2.0 [0.61]	TRD695SZRA14GRY-2	GRAY	2.0 [0.61]
TRD695SZRA14BLK-3	BLACK	3.0 [0.91]	TRD695SZRA14RD-3	RED	3.0 [0.91]	TRD695SZRA14GRY-3	GRAY	3.0 [0.91]
TRD695SZRA14BLK-5	BLACK	5.0 [1.52]	TRD695SZRA14RD-5	RED	5.0 [1.52]	TRD695SZRA14GRY-5	GRAY	5.0 [1.52]
TRD695SZRA14BLK-7	BLACK	7.0 [2.13]	TRD695SZRA14RD-7	RED	7.0 [2.13]	TRD695SZRA14GRY-7	GRAY	7.0 [2.13]
TRD695SZRA14BLK-10	BLACK	10.0 [3.05]	TRD695SZRA14RD-10	RED	10.0 [3.05]	TRD695SZRA14GRY-10	GRAY	10.0 [3.05]
TRD695SZRA14BLK-15	BLACK	15.0 [4.57]	TRD695SZRA14RD-15	RED	15.0 [4.57]	TRD695SZRA14GRY-15	GRAY	15.0 [4.57]
TRD695SZRA14BLK-20	BLACK	20.0 [6.10]	TRD695SZRA14RD-20	RED	20.0 [6.10]	TRD695SZRA14GRY-20	GRAY	20.0 [6.10]
TRD695SZRA14BLK-25	BLACK	25.0 [7.62]	TRD695SZRA14RD-25	RED	25.0 [7.62]	TRD695SZRA14GRY-25	GRAY	25.0 [7.62]
TRD695SZRA14BLK-30	BLACK	30.0 [9.14]	TRD695SZRA14RD-30	RED	30.0 [9.14]	TRD695SZRA14GRY-30	GRAY	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C6 LSZ FTP RGT-RGT			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TRD695SZRA14	REV. <b>D</b>
SCALE: NONE		CAD FILE: TRD695SZRA14.SLDDRW	SHEET 2 OF 2