


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	6/11/12	D. DESJARDIN
B	ECN6548: UPDATED NOTES. CHANGED PE NOTE TO LSZH	12/3/12	D. DESJARDIN
C	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/25/14	D. FRISIELLO



P1      **WIRING MAP**      P2

1	2	3	4	5	6	7	8	SHIELD
1	2	3	4	5	6	7	8	SHIELD
1 WHT/ORN	2 ORN	3 WHT/GRN	6 GRN	5 WHT/BLU	4 BLU	7 WHT/BRN	8 BRN	SHIELD

**NOTES:**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	APPROVALS DRAWN BY D. PARHAM CHECKED BY ENG APPROVED BY D. GALLAGHER	DATE 02/13/2012 06/11/2012 06/11/2012	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY <b>TELECOM/MODULAR</b>
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
	DWG. NO. <b>TRD695SZRA9</b>		SCALE: NONE	CAD FILE: TRD695SZRA9.SLDDRW
SHEET 1 OF 2		REV. <b>C</b>		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695SZRA9BLK-1	BLACK	1.0 [0.30]	TRD695SZRA9RD-1	RED	1.0 [0.30]	TRD695SZRA9GRY-1	GRAY	1.0 [0.30]
TRD695SZRA9BLK-2	BLACK	2.0 [0.61]	TRD695SZRA9RD-2	RED	2.0 [0.61]	TRD695SZRA9GRY-2	GRAY	2.0 [0.61]
TRD695SZRA9BLK-3	BLACK	3.0 [0.91]	TRD695SZRA9RD-3	RED	3.0 [0.91]	TRD695SZRA9GRY-3	GRAY	3.0 [0.91]
TRD695SZRA9BLK-5	BLACK	5.0 [1.52]	TRD695SZRA9RD-5	RED	5.0 [1.52]	TRD695SZRA9GRY-5	GRAY	5.0 [1.52]
TRD695SZRA9BLK-7	BLACK	7.0 [2.13]	TRD695SZRA9RD-7	RED	7.0 [2.13]	TRD695SZRA9GRY-7	GRAY	7.0 [2.13]
TRD695SZRA9BLK-10	BLACK	10.0 [3.05]	TRD695SZRA9RD-10	RED	10.0 [3.05]	TRD695SZRA9GRY-10	GRAY	10.0 [3.05]
TRD695SZRA9BLK-15	BLACK	15.0 [4.57]	TRD695SZRA9RD-15	RED	15.0 [4.57]	TRD695SZRA9GRY-15	GRAY	15.0 [4.57]
TRD695SZRA9BLK-20	BLACK	20.0 [6.10]	TRD695SZRA9RD-20	RED	20.0 [6.10]	TRD695SZRA9GRY-20	GRAY	20.0 [6.10]
TRD695SZRA9BLK-25	BLACK	25.0 [7.62]	TRD695SZRA9RD-25	RED	25.0 [7.62]	TRD695SZRA9GRY-25	GRAY	25.0 [7.62]
TRD695SZRA9BLK-30	BLACK	30.0 [9.14]	TRD695SZRA9RD-30	RED	30.0 [9.14]	TRD695SZRA9GRY-30	GRAY	30.0 [9.14]

**L-com** Global Connectivity 45 BEECHWOOD DRIVE  
NORTH ANDOVER, MA 01845

CATEGORY TELECOM/MODULAR

PRODUCT DESCRIPTION C6 LSZ FTP LFT-LFT

SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TRD695SZRA9	REV. <b>C</b>
------------------	--------------------------	-------------------------	------------------

SCALE: NONE | CAD FILE: TRD695SZRA9.SLDDRW | SHEET 2 OF 2