




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|-------------|
| REV. | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 12/16/2022 | DGUTTADAURO |





NOTES:

- CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLYBAG PER L-COM SPECIFICATION PS-0031.
- CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
- PLUG ORIENTATION FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:


EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | |
|--|--|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 |
| | DRAWN BY HBAKKE | 12/15/2022 | |
| | CHECKED BY DMAY | 12/16/2022 | |
| | APPROVED BY DGUST | 12/16/2022 | |
| THIRD-ANGLE PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION | CATEGORY |
|  | COLOR VARIATIONS MAY OCCUR | Category 6, Gigabit TAA Compliant Ethernet RJ45 - RJ45 Cable Assembly, 26AWG Stranded, SF/UTP Double Shielded Braid + Foil, LSZH | TELECOM/MODULAR |
| | SIZE A | CAGE CODE 43321 | ITEM NO. TRD695TAADSZ |
| | SCALE: NONE | CAD FILE: TRD695TAADSZ.SLDDRW | SHEET 1 OF 2 |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER/COLOR/LENGTH TABLE

| PART NUMBER | COLOR | LENGTH FEET [METERS] | LENGTH TOLERANCE FEET [METERS] |
|----------------------|-------|----------------------|--------------------------------|
| TRD695TAADSZ-BLK-3F | BLACK | 3.0 [.91] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-BLK-5F | BLACK | 5.0 [1.52] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-BLK-7F | BLACK | 7.0 [2.13] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-BLK-10F | BLACK | 10.0 [3.05] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLK-15F | BLACK | 15.0 [4.57] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLK-25F | BLACK | 25.0 [7.62] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLK-50F | BLACK | 50.0 [15.24] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLK-75F | BLACK | 75.0 [22.86] | + .4/-0 [+ .12/-0] |
| | | | |
| TRD695TAADSZ-BLU-3F | BLUE | 3.0 [.91] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-BLU-5F | BLUE | 5.0 [1.52] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-BLU-7F | BLUE | 7.0 [2.13] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-BLU-10F | BLUE | 10.0 [3.05] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLU-15F | BLUE | 15.0 [4.57] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLU-25F | BLUE | 25.0 [7.62] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLU-50F | BLUE | 50.0 [15.24] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-BLU-75F | BLUE | 75.0 [22.86] | + .4/-0 [+ .12/-0] |
| | | | |
| TRD695TAADSZ-GRY-3F | GRAY | 3.0 [.91] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-GRY-5F | GRAY | 5.0 [1.52] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-GRY-7F | GRAY | 7.0 [2.13] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-GRY-10F | GRAY | 10.0 [3.05] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-GRY-15F | GRAY | 15.0 [4.57] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-GRY-25F | GRAY | 25.0 [7.62] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-GRY-50F | GRAY | 50.0 [15.24] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-GRY-75F | GRAY | 75.0 [22.86] | + .4/-0 [+ .12/-0] |
| | | | |
| TRD695TAADSZ-RED-3F | RED | 3.0 [.91] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-RED-5F | RED | 5.0 [1.52] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-RED-7F | RED | 7.0 [2.13] | + .2/-0 [+ .06/-0] |
| TRD695TAADSZ-RED-10F | RED | 10.0 [3.05] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-RED-15F | RED | 15.0 [4.57] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-RED-25F | RED | 25.0 [7.62] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-RED-50F | RED | 50.0 [15.24] | + .4/-0 [+ .12/-0] |
| TRD695TAADSZ-RED-75F | RED | 75.0 [22.86] | + .4/-0 [+ .12/-0] |

| | | | |
|--|---------------------------|---|------------------|
|  | | 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | |
| CATEGORY <p style="text-align: center;">TELECOM/MODULAR</p> | | | |
| PRODUCT DESCRIPTION Category 6, Gigabit TAA Compliant Ethernet RJ45 - RJ45 Cable Assembly, 26AWG Stranded, SF/UTP Double Shielded Braid + Foil, LSZH | | | |
| SIZE A | CAGE CODE 43321 | ITEM NO. TRD695TAADSZ | REV. A |
| SCALE: NONE | | CAD FILE: TRD695TAADSZ.SLDDRW | |
| | | | SHEET 2 OF 2 |