




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/2022	DGUTTADAURO




NOTES:

- CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLYBAG PER L-COM SPECIFICATION PS-0031.
- CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
- PLUG ORIENTATION FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI™ brand 50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY HBAKKE		12/15/2022			
		CHECKED BY DMAY		12/16/2022			
		APPROVED BY DGUST		12/16/2022			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		FRACTIONS ± 1/32 ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR	
				PRODUCT DESCRIPTION		Category 6, Gigabit TAA Compliant Ethernet RJ45 to RJ45 Cable Assembly, 26AWG Stranded, U/FTP Foil Pair Shielded, CM PVC	
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. TRD695TAAS	REV. A
				SCALE: NONE		CAD FILE: TRD695TAAS.SLDDRW	
						SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER/COLOR/LENGTH TABLE

PART NUMBER	COLOR	LENGTH FEET [METERS]	LENGTH TOLERANCE FEET [METERS]
TRD695TAAS-BLK-3F	BLACK	3.0 [.91]	+2/-0 [+06/-0]
TRD695TAAS-BLK-5F	BLACK	5.0 [1.52]	+2/-0 [+06/-0]
TRD695TAAS-BLK-7F	BLACK	7.0 [2.13]	+2/-0 [+06/-0]
TRD695TAAS-BLK-10F	BLACK	10.0 [3.05]	+4/-0 [+12/-0]
TRD695TAAS-BLK-15F	BLACK	15.0 [4.57]	+4/-0 [+12/-0]
TRD695TAAS-BLK-25F	BLACK	25.0 [7.62]	+4/-0 [+12/-0]
TRD695TAAS-BLK-50F	BLACK	50.0 [15.24]	+4/-0 [+12/-0]
TRD695TAAS-BLK-75F	BLACK	75.0 [22.86]	+4/-0 [+12/-0]
TRD695TAAS-BLU-3F	BLUE	3.0 [.91]	+2/-0 [+06/-0]
TRD695TAAS-BLU-5F	BLUE	5.0 [1.52]	+2/-0 [+06/-0]
TRD695TAAS-BLU-7F	BLUE	7.0 [2.13]	+2/-0 [+06/-0]
TRD695TAAS-BLU-10F	BLUE	10.0 [3.05]	+4/-0 [+12/-0]
TRD695TAAS-BLU-15F	BLUE	15.0 [4.57]	+4/-0 [+12/-0]
TRD695TAAS-BLU-25F	BLUE	25.0 [7.62]	+4/-0 [+12/-0]
TRD695TAAS-BLU-50F	BLUE	50.0 [15.24]	+4/-0 [+12/-0]
TRD695TAAS-BLU-75F	BLUE	75.0 [22.86]	+4/-0 [+12/-0]
TRD695TAAS-GRN-3F	GREEN	3.0 [.91]	+2/-0 [+06/-0]
TRD695TAAS-GRN-5F	GREEN	5.0 [1.52]	+2/-0 [+06/-0]
TRD695TAAS-GRN-7F	GREEN	7.0 [2.13]	+2/-0 [+06/-0]
TRD695TAAS-GRN-10F	GREEN	10.0 [3.05]	+4/-0 [+12/-0]
TRD695TAAS-GRN-15F	GREEN	15.0 [4.57]	+4/-0 [+12/-0]
TRD695TAAS-GRN-25F	GREEN	25.0 [7.62]	+4/-0 [+12/-0]
TRD695TAAS-GRN-50F	GREEN	50.0 [15.24]	+4/-0 [+12/-0]
TRD695TAAS-GRN-75F	GREEN	75.0 [22.86]	+4/-0 [+12/-0]
TRD695TAAS-GRY-3F	GRAY	3.0 [.91]	+2/-0 [+06/-0]
TRD695TAAS-GRY-5F	GRAY	5.0 [1.52]	+2/-0 [+06/-0]
TRD695TAAS-GRY-7F	GRAY	7.0 [2.13]	+2/-0 [+06/-0]
TRD695TAAS-GRY-10F	GRAY	10.0 [3.05]	+4/-0 [+12/-0]
TRD695TAAS-GRY-15F	GRAY	15.0 [4.57]	+4/-0 [+12/-0]
TRD695TAAS-GRY-25F	GRAY	25.0 [7.62]	+4/-0 [+12/-0]
TRD695TAAS-GRY-50F	GRAY	50.0 [15.24]	+4/-0 [+12/-0]
TRD695TAAS-GRY-75F	GRAY	75.0 [22.86]	+4/-0 [+12/-0]
TRD695TAAS-RED-3F	RED	3.0 [.91]	+2/-0 [+06/-0]
TRD695TAAS-RED-5F	RED	5.0 [1.52]	+2/-0 [+06/-0]
TRD695TAAS-RED-7F	RED	7.0 [2.13]	+2/-0 [+06/-0]
TRD695TAAS-RED-10F	RED	10.0 [3.05]	+4/-0 [+12/-0]
TRD695TAAS-RED-15F	RED	15.0 [4.57]	+4/-0 [+12/-0]
TRD695TAAS-RED-25F	RED	25.0 [7.62]	+4/-0 [+12/-0]
TRD695TAAS-RED-50F	RED	50.0 [15.24]	+4/-0 [+12/-0]
TRD695TAAS-RED-75F	RED	75.0 [22.86]	+4/-0 [+12/-0]
TRD695TAAS-YLW-3F	YELLOW	3.0 [.91]	+2/-0 [+06/-0]
TRD695TAAS-YLW-5F	YELLOW	5.0 [1.52]	+2/-0 [+06/-0]
TRD695TAAS-YLW-7F	YELLOW	7.0 [2.13]	+2/-0 [+06/-0]
TRD695TAAS-YLW-10F	YELLOW	10.0 [3.05]	+4/-0 [+12/-0]
TRD695TAAS-YLW-15F	YELLOW	15.0 [4.57]	+4/-0 [+12/-0]
TRD695TAAS-YLW-25F	YELLOW	25.0 [7.62]	+4/-0 [+12/-0]
TRD695TAAS-YLW-50F	YELLOW	50.0 [15.24]	+4/-0 [+12/-0]
TRD695TAAS-YLW-75F	YELLOW	75.0 [22.86]	+4/-0 [+12/-0]

 an INFINIT® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
Category 6, Gigabit TAA Compliant Ethernet RJ45 to RJ45 Cable Assembly, 26AWG Stranded, U/FTP Foil Pair Shielded, CM PVC			
SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	TRD695TAAS	A
SCALE: NONE		CAD FILE: TRD695TAAS.SLDRW	SHEET 2 OF 2