




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |            |             |
|-----------|-----------------|------------|-------------|
| REV.      | DESCRIPTION     | DATE       | APPROVED    |
| A         | INITIAL RELEASE | 12/16/2022 | DGUTTADAURO |





**NOTES:**

- CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLYBAG PER L-COM SPECIFICATION PS-0031.
- CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.
- PLUG ORIENTATION FOR REFERENCE ONLY.

**REGULATORY COMPLIANCE:**


EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

|  |  |                               |  |
|--|--|-------------------------------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]   FRACTIONS ± 1/32<br>.XX = ± .02 [5]   ANGLES ± 1°<br>.XXX = ± .005 [13] | APPROVALS  | DATE                          | <br>50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |
|  | DRAWN BY<br>HBAKKE                                       | 12/15/2022                    |  |
|  | CHECKED BY<br>DMAY                                       | 12/16/2022                    |  |
|  | APPROVED BY<br>DGUST                                     | 12/16/2022                    |  |
| THIRD-ANGLE PROJECTION   | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY |                               | CATEGORY<br><b>TELECOM/MODULAR</b>   |
|   | COLOR VARIATIONS MAY OCCUR                               | SIZE<br><b>A</b>              | CAGE CODE<br><b>43321</b>  |
|  |  | ITEM NO.<br><b>TRD695TAAS</b> | REV.<br><b>A</b>   |
|  |  | SCALE: NONE                   | CAD FILE: TRD695TAAS.SLDRW<br>SHEET 1 OF 2   |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER/COLOR/LENGTH TABLE

| PART NUMBER        | COLOR  | LENGTH FEET [METERS] | LENGTH TOLERANCE FEET [METERS] |
|--------------------|--------|----------------------|--------------------------------|
| TRD695TAAS-BLK-3F  | BLACK  | 3.0 [.91]            | +2/-0 [+06/-0]                 |
| TRD695TAAS-BLK-5F  | BLACK  | 5.0 [1.52]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-BLK-7F  | BLACK  | 7.0 [2.13]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-BLK-10F | BLACK  | 10.0 [3.05]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLK-15F | BLACK  | 15.0 [4.57]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLK-25F | BLACK  | 25.0 [7.62]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLK-50F | BLACK  | 50.0 [15.24]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLK-75F | BLACK  | 75.0 [22.86]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLU-3F  | BLUE   | 3.0 [.91]            | +2/-0 [+06/-0]                 |
| TRD695TAAS-BLU-5F  | BLUE   | 5.0 [1.52]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-BLU-7F  | BLUE   | 7.0 [2.13]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-BLU-10F | BLUE   | 10.0 [3.05]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLU-15F | BLUE   | 15.0 [4.57]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLU-25F | BLUE   | 25.0 [7.62]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLU-50F | BLUE   | 50.0 [15.24]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-BLU-75F | BLUE   | 75.0 [22.86]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRN-3F  | GREEN  | 3.0 [.91]            | +2/-0 [+06/-0]                 |
| TRD695TAAS-GRN-5F  | GREEN  | 5.0 [1.52]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-GRN-7F  | GREEN  | 7.0 [2.13]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-GRN-10F | GREEN  | 10.0 [3.05]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRN-15F | GREEN  | 15.0 [4.57]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRN-25F | GREEN  | 25.0 [7.62]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRN-50F | GREEN  | 50.0 [15.24]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRN-75F | GREEN  | 75.0 [22.86]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRY-3F  | GRAY   | 3.0 [.91]            | +2/-0 [+06/-0]                 |
| TRD695TAAS-GRY-5F  | GRAY   | 5.0 [1.52]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-GRY-7F  | GRAY   | 7.0 [2.13]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-GRY-10F | GRAY   | 10.0 [3.05]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRY-15F | GRAY   | 15.0 [4.57]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRY-25F | GRAY   | 25.0 [7.62]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRY-50F | GRAY   | 50.0 [15.24]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-GRY-75F | GRAY   | 75.0 [22.86]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-RED-3F  | RED    | 3.0 [.91]            | +2/-0 [+06/-0]                 |
| TRD695TAAS-RED-5F  | RED    | 5.0 [1.52]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-RED-7F  | RED    | 7.0 [2.13]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-RED-10F | RED    | 10.0 [3.05]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-RED-15F | RED    | 15.0 [4.57]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-RED-25F | RED    | 25.0 [7.62]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-RED-50F | RED    | 50.0 [15.24]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-RED-75F | RED    | 75.0 [22.86]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-YLW-3F  | YELLOW | 3.0 [.91]            | +2/-0 [+06/-0]                 |
| TRD695TAAS-YLW-5F  | YELLOW | 5.0 [1.52]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-YLW-7F  | YELLOW | 7.0 [2.13]           | +2/-0 [+06/-0]                 |
| TRD695TAAS-YLW-10F | YELLOW | 10.0 [3.05]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-YLW-15F | YELLOW | 15.0 [4.57]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-YLW-25F | YELLOW | 25.0 [7.62]          | +4/-0 [+12/-0]                 |
| TRD695TAAS-YLW-50F | YELLOW | 50.0 [15.24]         | +4/-0 [+12/-0]                 |
| TRD695TAAS-YLW-75F | YELLOW | 75.0 [22.86]         | +4/-0 [+12/-0]                 |

|   |                           |   |                  |
|---|---------------------------|---|------------------|
|    |                           | 50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |                  |
| CATEGORY<br><p style="text-align: center;"><b>TELECOM/MODULAR</b></p>   |                           |   |                  |
| PRODUCT DESCRIPTION<br>Category 6, Gigabit TAA Compliant Ethernet RJ45 to RJ45 Cable Assembly, 26AWG Stranded, U/FTP Foil Pair Shielded, CM PVC |                           |   |                  |
| SIZE<br><b>A</b>  | CAGE CODE<br><b>43321</b> | ITEM NO.<br><b>TRD695TAAS</b>   | REV.<br><b>A</b> |
| SCALE: NONE   |                           | CAD FILE: TRD695TAAS.SLDDRW   |                  |
|   |                           |   | SHEET 2 OF 2     |