



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/21/2021	D.GUTTADAURO



WIRING MAP



PART NUMBER	LENGTH METERS [FEET]
TRD795BLK-05M	0.50 [1.64]
TRD795BLK-1M	1.0 [3.28]
TRD795BLK-2M	2.0 [6.56]
TRD795BLK-3M	3.0 [9.84]
TRD795BLK-5M	5.0 [16.41]
TRD795BLK-7.5M	7.5 [24.61]
TRD795BLK-10M	10.0 [32.81]
TRD795BLK-15M	15.0 [49.21]

NOTES:

- LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
- PLUG CONFORMS TO TIA-1096.
- CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS DATE DRAWN BY B.ZHANG 12/04/2020 CHECKED BY SPAN 12/04/2020 APPROVED BY DGUTTADAURO 12/04/2020	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 CATEGORY TELECOM/MODULAR PRODUCT DESCRIPTION CA,CAT7 S/FTP RJ45 TO RJ45 PVC JKT,BLK
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR SIZE A CAGE CODE 43321 DWG. NO. TRD795BLK REV. A SCALE: NONE CAD FILE: TRD795BLK.SLDDRW SHEET 1 OF 1	