

6

5

4

3

2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	12/06/2023	BZHANG	GUTTADAURO

F

F

E

E

D

D

C


C

B


B

A

A



P1 WIRING MAP P2





NOTES:

- 1.LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
- 2.PLUG CONFORMS TO TIA-1096.
- 3.CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
- 4.CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PART NUMBER	LENGTH METERS[FEET]
TRD795GRN-05M	0.5[1.64]
TRD795GRN-1M	1.0[3.28]
TRD795GRN-2M	2.0[6.56]
TRD795GRN-3M	3.0[9.84]
TRD795GRN-5M	5.0[16.41]
TRD795GRN-7.5M	7.5[24.61]
TRD795GRN-10M	10.0[32.81]
TRD795GRN-15M	15.0[49.21]

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		 an INFINIT@ brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [0.5] ANGLES ± 1° .XXX = ±.005 [0.13]				SCALE	SHEET
CABLE LENGTH TOLERANCES UNLESS OTHERWISE SPECIFIED: ≤12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		NONE		1 OF 1	
DESCRIPTION					
CA,CAT7 S/FTP RJ45 TO RJ45 PVC JKT,GRN					
SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV	
A	43321	BZHANG	TRD795GRN	A	

6

5

4

3

2

1